

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276519

Luminaire Tested: P3AS17R459835DE010 E3DL1H

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1276519  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R459835DE010 E3DL1H  
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DL1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1371.0 lumens  
Efficiency: N/A  
Efficacy: 67.2 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276519

CATALOG NUMBER: P3AS17R459835DE010 E3DL1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1276519

CATALOG NUMBER: P3AS17R459835DE010 E3DL1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 |  | 101 | 100 | 99  |  | 98  |
| 2   | 109 | 104 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 96  | 94  |  | 96  | 94  | 92  |  | 93  |
| 3   | 104 | 98  | 93  | 89  | 102 | 96  | 92  | 88  | 94  | 90  | 87  |  | 91  | 88  | 86  |  | 89  |
| 4   | 99  | 92  | 87  | 83  | 97  | 91  | 86  | 82  | 89  | 85  | 81  |  | 87  | 83  | 80  |  | 85  |
| 5   | 94  | 87  | 81  | 77  | 93  | 86  | 81  | 77  | 84  | 80  | 76  |  | 82  | 79  | 76  |  | 81  |
| 6   | 90  | 82  | 76  | 73  | 89  | 81  | 76  | 72  | 80  | 75  | 72  |  | 78  | 74  | 71  |  | 77  |
| 7   | 86  | 78  | 72  | 68  | 85  | 77  | 72  | 68  | 76  | 71  | 68  |  | 75  | 71  | 67  |  | 74  |
| 8   | 83  | 74  | 68  | 65  | 82  | 73  | 68  | 64  | 72  | 68  | 64  |  | 71  | 67  | 64  |  | 70  |
| 9   | 79  | 70  | 65  | 61  | 78  | 70  | 65  | 61  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 67  |
| 10  | 76  | 67  | 62  | 58  | 75  | 67  | 62  | 58  | 66  | 61  | 58  |  | 65  | 61  | 58  |  | 65  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 514849 |
| 5°  | 502794 |
| 10° | 462205 |
| 15° | 391625 |
| 20° | 303850 |
| 25° | 212407 |
| 30° | 133793 |
| 35° | 78782  |
| 40° | 44569  |
| 45° | 21677  |
| 50° | 7539   |
| 55° | 6079   |
| 60° | 5921   |
| 65° | 5707   |
| 70° | 5514   |
| 75° | 5168   |
| 80° | 4672   |
| 85° | 3019   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21677 cd/sqm

TEST NUMBER: P1276519

CATALOG NUMBER: P3AS17R459835DE010 E3DL1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 211.4  | 15.4      |
| 10°-20°   | 473.7  | 34.6      |
| 20°-30°   | 402.3  | 29.3      |
| 30°-40°   | 191.9  | 14.0      |
| 40°-50°   | 57.8   | 4.2       |
| 50°-60°   | 14.7   | 1.1       |
| 60°-70°   | 10.9   | 0.8       |
| 70°-80°   | 6.5    | 0.5       |
| 80°-90°   | 1.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 1087.4 | 79.3      |
| 0°-40°    | 1279.3 | 93.3      |
| 0°-60°    | 1351.8 | 98.6      |
| 0°-90°    | 1371.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1371.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2348 |      |
| 5°  | 2284 | 211  |
| 15° | 1725 | 474  |
| 25° | 878  | 402  |
| 35° | 294  | 192  |
| 45° | 70   | 58   |
| 55° | 16   | 15   |
| 65° | 11   | 11   |
| 75° | 6    | 6    |
| 85° | 1    | 2    |
| 90° | 0    |      |

TEST NUMBER: P1276519

CATALOG NUMBER: P3AS17R459835DE010 E3DL1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2347.9 |
| 2.5°  | 2333.2 |
| 5°    | 2284.2 |
| 7.5°  | 2199.6 |
| 10°   | 2075.8 |
| 12.5° | 1911.5 |
| 15°   | 1725.1 |
| 17.5° | 1517.9 |
| 20°   | 1302.1 |
| 22.5° | 1082.6 |
| 25°   | 877.9  |
| 27.5° | 691.5  |
| 30°   | 528.4  |
| 32.5° | 397.2  |
| 35°   | 294.3  |
| 37.5° | 217.0  |
| 40°   | 155.7  |
| 42.5° | 107.9  |
| 45°   | 69.9   |
| 47.5° | 39.2   |
| 50°   | 22.1   |
| 52.5° | 17.2   |
| 55°   | 15.9   |
| 57.5° | 14.7   |
| 60°   | 13.5   |
| 62.5° | 12.3   |
| 65°   | 11.0   |
| 67.5° | 9.8    |
| 70°   | 8.6    |
| 72.5° | 7.4    |
| 75°   | 6.1    |
| 77.5° | 4.9    |
| 80°   | 3.7    |
| 82.5° | 2.5    |
| 85°   | 1.2    |
| 87.5° | 1.2    |
| 90°   | 0.0    |

(END OF REPORT)