

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276540

Luminaire Tested: P3AS17R509835DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276540
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R509835DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1679.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276540
CATALOG NUMBER: P3AS17R509835DE010 E3CD1MMS

Luminous Intensity Polar Plot





TEST NUMBER: P1276540
 CATALOG NUMBER: P3AS17R509835DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95				95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90				90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85				85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80				80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76				76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72				72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69				69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65				65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62				62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59				59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584756
5°	574289
10°	551404
15°	505633
20°	445869
25°	341754
30°	185826
35°	59776
40°	14055
45°	1892
50°	1672
55°	1873
60°	1623
65°	1920
70°	1603
75°	2118
80°	1515
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 85°
 Luminance: 3019 cd/sqm



TEST NUMBER: P1276540
 CATALOG NUMBER: P3AS17R509835DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.8	14.6
10°-20°	619.1	36.9
20°-30°	620.1	36.9
30°-40°	174.3	10.4
40°-50°	10.5	0.6
50°-60°	4.0	0.2
60°-70°	3.2	0.2
70°-80°	2.1	0.1
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1484.0	88.4
0°-40°	1658.4	98.8
0°-60°	1672.9	99.6
0°-90°	1679.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1679.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2667	
5°	2609	245
15°	2227	619
25°	1412	620
35°	223	174
45°	6	11
55°	5	4
65°	4	3
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1276540
CATALOG NUMBER: P3AS17R509835DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2666.7
2.5°	2653.2
5°	2609.0
7.5°	2548.8
10°	2476.4
12.5°	2367.2
15°	2227.3
17.5°	2066.6
20°	1910.7
22.5°	1716.8
25°	1412.5
27.5°	1051.7
30°	733.9
32.5°	443.0
35°	223.3
37.5°	105.5
40°	49.1
42.5°	18.4
45°	6.1
47.5°	4.9
50°	4.9
52.5°	4.9
55°	4.9
57.5°	3.7
60°	3.7
62.5°	3.7
65°	3.7
67.5°	2.5
70°	2.5
72.5°	2.5
75°	2.5
77.5°	1.2
80°	1.2
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)