

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275514

Luminaire Tested: P3AS05R509835DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R509835DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 435.0 lumens
Efficiency: N/A
Efficacy: 60.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275514
CATALOG NUMBER: P3AS05R509835DE010 E3DL1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1275514
 CATALOG NUMBER: P3AS05R509835DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94			
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82			
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76			
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72			
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67			
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64			
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60			
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57			
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	138498
5°	135703
10°	127119
15°	113803
20°	95768
25°	73093
30°	47501
35°	28161
40°	16288
45°	8156
50°	3036
55°	2370
60°	2193
65°	2024
70°	1988
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8156 cd/sqm



TEST NUMBER: P1275514
 CATALOG NUMBER: P3AS05R509835DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.4	13.2
10°-20°	138.6	31.9
20°-30°	136.0	31.3
30°-40°	68.5	15.8
40°-50°	21.7	5.0
50°-60°	5.6	1.3
60°-70°	4.0	0.9
70°-80°	2.4	0.6
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	332.0	76.3
0°-40°	400.5	92.1
0°-60°	427.8	98.3
0°-90°	435.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	435.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	632	
5°	616	57
15°	501	139
25°	302	136
35°	105	69
45°	26	22
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1275514
CATALOG NUMBER: P3AS05R509835DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	631.6
2.5°	627.7
5°	616.5
7.5°	596.4
10°	570.9
12.5°	538.0
15°	501.3
17.5°	458.7
20°	410.4
22.5°	358.1
25°	302.1
27.5°	242.5
30°	187.6
32.5°	141.2
35°	105.2
37.5°	77.7
40°	56.9
42.5°	40.2
45°	26.3
47.5°	15.1
50°	8.9
52.5°	6.6
55°	6.2
57.5°	5.4
60°	5.0
62.5°	4.6
65°	3.9
67.5°	3.5
70°	3.1
72.5°	2.7
75°	2.3
77.5°	1.9
80°	1.5
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)