

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276607

Luminaire Tested: P3AS17R609835DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276607
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R609835DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1290.0 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276607

CATALOG NUMBER: P3AS17R609835DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1276607

CATALOG NUMBER: P3AS17R609835DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304603
5°	301716
10°	292936
15°	274440
20°	242898
25°	203213
30°	159265
35°	115536
40°	76858
45°	47912
50°	25927
55°	7493
60°	6973
65°	6382
70°	6283
75°	6270
80°	6188
85°	6290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 47912 cd/sqm

TEST NUMBER: P1276607

CATALOG NUMBER: P3AS17R609835DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.1	10.0
10°-20°	335.4	26.0
20°-30°	382.3	29.6
30°-40°	271.1	21.0
40°-50°	123.0	9.5
50°-60°	26.1	2.0
60°-70°	12.6	1.0
70°-80°	7.8	0.6
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.8	65.6
0°-40°	1117.9	86.7
0°-60°	1267.0	98.2
0°-90°	1290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1290.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1389	
5°	1371	129
15°	1209	335
25°	840	382
35°	432	271
45°	154	123
55°	20	26
65°	12	13
75°	7	8
85°	2	3
90°	0	

TEST NUMBER: P1276607

CATALOG NUMBER: P3AS17R609835DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1389.1
2.5°	1384.2
5°	1370.7
7.5°	1347.5
10°	1315.6
12.5°	1270.2
15°	1208.9
17.5°	1131.7
20°	1040.9
22.5°	942.8
25°	839.9
27.5°	734.4
30°	629.0
32.5°	528.4
35°	431.6
37.5°	345.8
40°	268.5
42.5°	203.5
45°	154.5
47.5°	115.3
50°	76.0
52.5°	35.6
55°	19.6
57.5°	17.2
60°	15.9
62.5°	14.7
65°	12.3
67.5°	11.0
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	4.9
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

(END OF REPORT)