

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275626

Luminaire Tested: P3AS05R709835DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275626
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-17)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709835DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 461.1 lumens
Efficiency: N/A
Efficacy: 64.0 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 1.06
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275626
CATALOG NUMBER: P3AS05R709835DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275626
 CATALOG NUMBER: P3AS05R709835DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	81	86	83	80	79	79	79	79
4	95	87	81	77	94	86	81	76	84	79	76	82	78	75	80	77	74	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	63	59	68	63	59	67	62	58	66	61	58	57	57	57	57
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52	52	52	52
9	72	61	55	51	71	61	55	51	60	54	50	59	54	50	58	53	50	49	49	49	49
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45	45	45	45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	89642
5°	84525
10°	80137
15°	78706
20°	75863
25°	71520
30°	70998
35°	61837
40°	39989
45°	18917
50°	2661
55°	229
60°	175
65°	208
70°	128
75°	169
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18917 cd/sqm



TEST NUMBER: P1275626
 CATALOG NUMBER: P3AS05R709835DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	7.8
10°-20°	97.4	21.1
20°-30°	137.7	29.9
30°-40°	138.4	30.0
40°-50°	49.8	10.8
50°-60°	1.3	0.3
60°-70°	0.3	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.9	58.8
0°-40°	409.4	88.8
0°-60°	460.5	99.9
0°-90°	461.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	461.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	409	
5°	384	36
15°	347	97
25°	296	138
35°	231	138
45°	61	50
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275626
CATALOG NUMBER: P3AS05R709835DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	408.8
1°	407.6
2°	404.1
3°	398.4
4°	391.2
5°	384.0
6°	377.2
7°	371.9
8°	367.1
9°	363.3
10°	359.9
11°	357.1
12°	354.4
13°	351.8
14°	349.3
15°	346.7
16°	343.5
17°	340.1
18°	335.9
19°	330.8
20°	325.1
21°	318.8
22°	312.6
23°	306.5
24°	300.7
25°	295.6
26°	292.0
27°	289.1
28°	286.8
29°	284.2
30°	280.4
31°	274.9
32°	267.2
32.5°	262.8
33°	256.9
34°	245.4
35°	231.0
36°	215.1
37°	197.1
37.5°	188.8
38°	177.4
39°	157.2
40°	139.7
42.5°	96.8
45°	61.0



TEST NUMBER: P1275626
CATALOG NUMBER: P3AS05R709835DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	32.8
50°	7.8
52.5°	0.9
55°	0.6
57.5°	0.6
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.2
70°	0.2
72.5°	0.2
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)