

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276608

Luminaire Tested: P3AS17R609835DE010 E3DL1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276608  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS17R609835DE010 E3DL1MW  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1290.0 lumens  
Efficiency: N/A  
Efficacy: 63.2 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 20.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276608  
CATALOG NUMBER: P3AS17R609835DE010 E3DL1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1276608

CATALOG NUMBER: P3AS17R609835DE010 E3DL1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	67	63	60	59	59	59	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	304603
5°	301716
10°	292936
15°	274440
20°	242898
25°	203213
30°	159265
35°	115536
40°	76858
45°	47912
50°	25927
55°	7493
60°	6973
65°	6382
70°	6283
75°	6270
80°	6188
85°	6290

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 47912 cd/sqm



TEST NUMBER: P1276608  
 CATALOG NUMBER: P3AS17R609835DE010 E3DL1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.1	10.0
10°-20°	335.4	26.0
20°-30°	382.3	29.6
30°-40°	271.1	21.0
40°-50°	123.0	9.5
50°-60°	26.1	2.0
60°-70°	12.6	1.0
70°-80°	7.8	0.6
80°-90°	2.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	846.8	65.6
0°-40°	1117.9	86.7
0°-60°	1267.0	98.2
0°-90°	1290.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1290.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1389	
5°	1371	129
15°	1209	335
25°	840	382
35°	432	271
45°	154	123
55°	20	26
65°	12	13
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P1276608  
CATALOG NUMBER: P3AS17R609835DE010 E3DL1MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1389.1
2.5°	1384.2
5°	1370.7
7.5°	1347.5
10°	1315.6
12.5°	1270.2
15°	1208.9
17.5°	1131.7
20°	1040.9
22.5°	942.8
25°	839.9
27.5°	734.4
30°	629.0
32.5°	528.4
35°	431.6
37.5°	345.8
40°	268.5
42.5°	203.5
45°	154.5
47.5°	115.3
50°	76.0
52.5°	35.6
55°	19.6
57.5°	17.2
60°	15.9
62.5°	14.7
65°	12.3
67.5°	11.0
70°	9.8
72.5°	8.6
75°	7.4
77.5°	6.1
80°	4.9
82.5°	3.7
85°	2.5
87.5°	1.2
90°	0.0

(END OF REPORT)