

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275634

Luminaire Tested: P3AS05R709835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R709835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 136.0 lumens
Efficiency: N/A
Efficacy: 18.9 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275634

CATALOG NUMBER: P3AS05R709835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275634

CATALOG NUMBER: P3AS05R709835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	104	110	107	105	103	103	101	100		100	98	97		96
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90
3	100	93	88	83	98	92	87	83	89	85	81		87	83	80		84
4	95	86	80	76	93	85	80	75	83	78	74		81	77	73		79
5	89	80	74	69	88	79	73	69	78	72	68		76	71	68		74
6	85	75	68	64	83	74	68	64	73	67	63		71	66	63		70
7	80	70	64	59	79	69	63	59	68	62	58		67	62	58		66
8	76	66	59	55	75	65	59	55	64	58	54		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	51		58
10	69	58	52	48	67	58	52	48	57	51	48		56	51	48		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31905
5°	31323
10°	29525
15°	26788
20°	23452
25°	19767
30°	16180
35°	12555
40°	8988
45°	5706
50°	2831
55°	1720
60°	1491
65°	1349
70°	1218
75°	1101
80°	1010
85°	1006

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5706 cd/sqm

TEST NUMBER: P1275634

CATALOG NUMBER: P3AS05R709835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	13.3	9.8
10°-20°	32.8	24.2
20°-30°	37.4	27.5
30°-40°	29.2	21.5
40°-50°	14.4	10.6
50°-60°	4.4	3.2
60°-70°	2.6	1.9
70°-80°	1.4	1.0
80°-90°	0.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	83.5	61.4
0°-40°	112.8	82.9
0°-60°	131.6	96.7
0°-90°	136.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	136.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	146	
5°	142	13
15°	118	33
25°	82	37
35°	47	29
45°	18	14
55°	4	4
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1275634

CATALOG NUMBER: P3AS05R709835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	145.5
2.5°	144.7
5°	142.3
7.5°	138.3
10°	132.6
12.5°	126.0
15°	118.0
17.5°	109.5
20°	100.5
22.5°	91.0
25°	81.7
27.5°	72.6
30°	63.9
32.5°	55.2
35°	46.9
37.5°	39.0
40°	31.4
42.5°	24.4
45°	18.4
47.5°	12.9
50°	8.3
52.5°	5.5
55°	4.5
57.5°	4.0
60°	3.4
62.5°	3.0
65°	2.6
67.5°	2.3
70°	1.9
72.5°	1.5
75°	1.3
77.5°	1.1
80°	0.8
82.5°	0.6
85°	0.4
87.5°	0.2
90°	0.0

(END OF REPORT)