

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276623

Luminaire Tested: P3AS17R659835DE010 E3CB1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-44)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659835DE010 E3CB1MB
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3CB1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 74.4 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.9
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276623

CATALOG NUMBER: P3AS17R659835DE010 E3CB1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1276623

CATALOG NUMBER: P3AS17R659835DE010 E3CB1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94		
2	108	103	99	96	106	101	98	95	98	95	93	95	93	91	92	90	89	87		
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81		
4	97	90	84	80	96	89	84	80	87	82	79	85	81	78	83	80	77	75		
5	93	84	78	74	91	83	78	74	82	77	73	80	76	73	78	75	72	70		
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66		
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62		
8	80	70	64	60	78	69	64	60	68	63	60	67	63	59	66	62	59	58		
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54		
10	72	63	57	53	71	62	57	53	61	56	53	60	56	53	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	370716
5°	348910
10°	344483
15°	338390
20°	319508
25°	296533
30°	230491
35°	133338
40°	53729
45°	24716
50°	9620
55°	3747
60°	3245
65°	3165
70°	3142
75°	3135
80°	3157
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24716 cd/sqm

TEST NUMBER: P1276623

CATALOG NUMBER: P3AS17R659835DE010 E3CB1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	9.9
10°-20°	416.3	27.4
20°-30°	544.9	35.9
30°-40°	315.6	20.8
40°-50°	67.5	4.5
50°-60°	11.0	0.7
60°-70°	6.1	0.4
70°-80°	3.6	0.2
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1111.9	73.3
0°-40°	1427.5	94.1
0°-60°	1506.0	99.3
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1691	
5°	1585	151
15°	1491	416
25°	1226	545
35°	498	316
45°	80	68
55°	10	11
65°	6	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1276623

CATALOG NUMBER: P3AS17R659835DE010 E3CB1MB

CANDELA DISTRIBUTION (FULL):

0°	
0°	1690.6
2.5°	1642.8
5°	1585.1
7.5°	1561.8
10°	1547.1
12.5°	1526.2
15°	1490.6
17.5°	1435.4
20°	1369.2
22.5°	1306.6
25°	1225.6
27.5°	1089.5
30°	910.3
32.5°	705.4
35°	498.1
37.5°	315.3
40°	187.7
42.5°	117.8
45°	79.7
47.5°	51.5
50°	28.2
52.5°	13.5
55°	9.8
57.5°	8.6
60°	7.4
62.5°	7.4
65°	6.1
67.5°	4.9
70°	4.9
72.5°	3.7
75°	3.7
77.5°	2.5
80°	2.5
82.5°	1.2
85°	1.2
87.5°	1.2
90°	0.0

(END OF REPORT)