

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275683

Luminaire Tested: P3AS09R209835DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R209835DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 715.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275683
CATALOG NUMBER: P3AS09R209835DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275683
 CATALOG NUMBER: P3AS09R209835DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	99	100
1	115	114	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	99	98	96	97
2	112	109	106	104	110	107	105	103	104	102	101	101	100	98	99	98	96	97	95	94	95
3	109	105	102	99	107	104	101	98	101	99	97	99	97	95	97	95	94	97	95	94	93
4	106	101	98	95	105	100	97	95	99	96	94	97	95	93	95	93	92	95	93	92	91
5	104	98	95	92	102	98	94	92	96	93	91	95	92	90	93	91	90	93	91	90	89
6	101	96	92	89	100	95	92	89	94	91	89	93	90	88	92	89	88	92	89	88	87
7	99	93	90	87	98	93	89	87	92	89	86	91	88	86	90	87	86	90	87	86	85
8	97	91	87	85	96	91	87	85	90	87	85	89	86	84	88	86	84	88	86	84	83
9	95	89	85	83	94	89	85	83	88	85	83	87	84	83	87	84	82	87	84	82	81
10	93	87	84	81	92	87	83	81	86	83	81	86	83	81	85	83	81	85	83	81	80

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1084606
5°	913183
10°	570375
15°	213236
20°	73203
25°	30510
30°	14357
35°	6425
40°	3034
45°	1551
50°	580
55°	115
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1551 cd/sqm



TEST NUMBER: P1275683
 CATALOG NUMBER: P3AS09R209835DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.0	48.2
10°-20°	284.2	39.7
20°-30°	64.6	9.0
30°-40°	16.4	2.3
40°-50°	4.1	0.6
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.7	97.0
0°-40°	710.2	99.3
0°-60°	714.8	100.0
0°-90°	715.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4946	
5°	4149	345
15°	939	284
25°	126	65
35°	24	16
45°	5	4
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275683
CATALOG NUMBER: P3AS09R209835DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	4946.2
1°	4904.2
2°	4780.7
3°	4603.4
4°	4385.9
5°	4148.6
6°	3884.1
7°	3592.3
8°	3251.8
9°	2914.4
10°	2561.6
11°	2186.1
12°	1811.2
13°	1493.7
14°	1190.1
15°	939.3
16°	741.4
17°	584.8
18°	469.9
19°	382.2
20°	313.7
21°	262.2
22°	218.9
23°	182.0
24°	151.8
25°	126.1
27.5°	82.5
30°	56.7
32.5°	34.9
35°	24.0
37.5°	15.4
40°	10.6
42.5°	7.3
45°	5.0
47.5°	3.4
50°	1.7
52.5°	0.8
55°	0.3
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1275683
CATALOG NUMBER: P3AS09R209835DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)