

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276634

Luminaire Tested: P3AS17R659835DE010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276634
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS17R659835DE010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 603.0 lumens
Efficiency: N/A
Efficacy: 29.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276634

CATALOG NUMBER: P3AS17R659835DE010 E3DL1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276634

CATALOG NUMBER: P3AS17R659835DE010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	84	90	86	83		88	85	82		86
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		81
5	91	82	76	71	89	81	75	71	79	74	70		77	73	70		76
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		72
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67
8	77	67	61	57	76	67	61	57	66	60	57		65	60	56		64
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		60
10	70	60	54	50	69	59	54	50	59	53	50		58	53	50		57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142204
5°	140502
10°	135157
15°	126630
20°	113877
25°	96707
30°	75632
35°	53886
40°	35266
45°	21801
50°	11087
55°	3900
60°	3421
65°	3424
70°	3077
75°	3050
80°	3031
85°	3019

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 21801 cd/sqm

TEST NUMBER: P1276634

CATALOG NUMBER: P3AS17R659835DE010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.9	9.9
10°-20°	155.2	25.7
20°-30°	181.4	30.1
30°-40°	126.8	21.0
40°-50°	55.8	9.3
50°-60°	12.4	2.1
60°-70°	6.3	1.0
70°-80°	3.8	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	396.6	65.8
0°-40°	523.3	86.8
0°-60°	591.6	98.1
0°-90°	603.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	603.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	648	
5°	638	60
15°	558	155
25°	400	181
35°	201	127
45°	70	56
55°	10	12
65°	7	6
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1276634

CATALOG NUMBER: P3AS17R659835DE010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	648.5
2.5°	646.1
5°	638.3
7.5°	625.1
10°	607.0
12.5°	584.8
15°	557.8
17.5°	524.7
20°	488.0
22.5°	446.6
25°	399.7
27.5°	350.4
30°	298.7
32.5°	248.8
35°	201.3
37.5°	159.9
40°	123.2
42.5°	93.2
45°	70.3
47.5°	51.7
50°	32.5
52.5°	16.8
55°	10.2
57.5°	9.0
60°	7.8
62.5°	7.2
65°	6.6
67.5°	5.4
70°	4.8
72.5°	4.2
75°	3.6
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)