

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275724

Luminaire Tested: P3AS09R259835DE010 E3DLP1H

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1275724  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-9)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R259835DE010 E3DLP1H  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 366.0 lumens  
Efficiency: N/A  
Efficacy: 33.3 lumens/watt  
Spacing Criteria (0/90/45): 0.62 / 0.62 / 0.68  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 11  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1275724  
CATALOG NUMBER: P3AS09R259835DE010 E3DLP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P1275724  
 CATALOG NUMBER: P3AS09R259835DE010 E3DLP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	104	104	102	101	100	99	98	97	96	95	93	93	93	93
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86	86	86	86
3	102	95	90	86	100	94	89	86	91	87	84	89	86	83	87	84	82	80	80	80	80
4	97	89	84	79	95	88	83	79	86	81	78	84	80	77	82	79	76	75	75	75	75
5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	66	66	66	66
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62	62	62	62
8	80	70	65	60	79	70	64	60	69	64	60	68	63	60	67	63	60	58	58	58	58
9	76	67	61	57	75	66	61	57	65	60	57	65	60	57	64	59	56	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	132884
5°	127493
10°	111688
15°	89762
20°	68979
25°	52188
30°	37702
35°	25056
40°	15200
45°	8838
50°	5629
55°	4588
60°	3991
65°	3528
70°	2949
75°	2881
80°	2147
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 8838 cd/sqm



TEST NUMBER: P1275724  
 CATALOG NUMBER: P3AS09R259835DE010 E3DLP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	52.7	14.4
10°-20°	109.3	29.9
20°-30°	98.9	27.0
30°-40°	59.4	16.2
40°-50°	23.6	6.4
50°-60°	10.9	3.0
60°-70°	6.6	1.8
70°-80°	3.5	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.0	71.3
0°-40°	320.4	87.5
0°-60°	354.8	97.0
0°-90°	366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	366.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	606	
5°	579	53
15°	395	109
25°	216	99
35°	94	59
45°	28	24
55°	12	11
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1275724  
CATALOG NUMBER: P3AS09R259835DE010 E3DLP1H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	606.0
1°	606.0
2°	603.1
3°	596.8
4°	588.9
5°	579.2
6°	566.6
7°	552.3
8°	535.8
9°	519.2
10°	501.6
11°	481.0
12°	459.9
13°	438.8
14°	417.7
15°	395.4
17.5°	342.9
20°	295.6
22.5°	252.8
25°	215.7
27.5°	180.9
30°	148.9
32.5°	119.8
35°	93.6
37.5°	71.3
40°	53.1
42.5°	38.8
45°	28.5
47.5°	21.7
50°	16.5
52.5°	13.7
55°	12.0
57.5°	10.3
60°	9.1
62.5°	7.4
65°	6.8
67.5°	5.7
70°	4.6
72.5°	4.0
75°	3.4
77.5°	2.9
80°	1.7
82.5°	1.1
85°	1.1
87.5°	0.6



TEST NUMBER: P1275724  
CATALOG NUMBER: P3AS09R259835DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):



(END OF REPORT)