

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275741

Luminaire Tested: P3AS09R309835DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275741
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309835DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 720.0 lumens
Efficiency: N/A
Efficacy: 65.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275741
CATALOG NUMBER: P3AS09R309835DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1275741
 CATALOG NUMBER: P3AS09R309835DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	96	95	94
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	95	93	92	90
3	108	103	100	97	106	102	99	96	99	97	95	97	95	93	95	93	92	93	91	89	88
4	105	99	95	92	103	98	95	92	96	93	91	94	92	90	93	91	89	90	88	86	85
5	101	96	92	89	100	95	91	88	93	90	87	92	89	87	90	88	86	88	85	83	82
6	99	92	88	85	97	92	88	85	90	87	84	89	86	84	88	85	83	86	83	81	80
7	96	89	85	82	95	89	85	82	88	84	82	87	84	81	86	83	81	84	81	79	78
8	93	87	83	80	92	86	82	80	85	82	79	84	81	79	84	81	79	82	79	77	76
9	91	84	80	77	90	84	80	77	83	79	77	82	79	77	82	79	77	80	77	75	74
10	88	82	78	75	88	81	78	75	81	77	75	80	77	75	80	77	75	80	77	75	74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	572849
5°	565374
10°	493623
15°	313759
20°	124307
25°	41519
30°	19319
35°	8754
40°	3349
45°	1644
50°	478
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1644 cd/sqm



TEST NUMBER: P1275741
 CATALOG NUMBER: P3AS09R309835DE010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.8	32.6
10°-20°	364.2	50.6
20°-30°	93.9	13.0
30°-40°	22.1	3.1
40°-50°	4.3	0.6
50°-60°	0.5	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	692.9	96.2
0°-40°	715.0	99.3
0°-60°	719.8	100.0
0°-90°	720.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2612	
5°	2568	235
15°	1382	364
25°	172	94
35°	33	22
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1275741
CATALOG NUMBER: P3AS09R309835DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2612.4
1°	2610.5
2°	2604.3
3°	2597.3
4°	2587.0
5°	2568.5
6°	2538.6
7°	2488.9
8°	2421.0
9°	2332.4
10°	2216.9
11°	2079.7
12°	1929.9
13°	1757.5
14°	1576.9
15°	1382.1
16°	1191.2
17°	1007.3
18°	830.9
19°	669.1
20°	532.7
21°	419.2
22°	329.8
23°	261.0
24°	209.1
25°	171.6
26°	143.1
27°	121.6
28°	105.1
29°	90.0
30°	76.3
32.5°	48.1
35°	32.7
37.5°	20.4
40°	11.7
42.5°	7.8
45°	5.3
47.5°	3.1
50°	1.4
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3



TEST NUMBER: P1275741
CATALOG NUMBER: P3AS09R309835DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)