

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276718

Luminaire Tested: P3AS20R209835D010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276718
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R209835D010 E3D1WH
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1998.0 lumens
Efficiency: N/A
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276718

CATALOG NUMBER: P3AS20R209835D010 E3D1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1276718

CATALOG NUMBER: P3AS20R209835D010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	114	112	110	113	111	110	108	107	106	105		104	103	102		100
2	112	109	106	104	110	107	105	103	104	102	101		101	100	98		99
3	109	105	102	99	107	104	101	98	101	99	97		99	97	95		97
4	106	101	98	95	105	100	97	95	99	96	94		97	95	93		95
5	104	98	95	92	102	98	94	92	96	93	91		95	92	90		93
6	101	96	92	89	100	95	92	89	94	91	89		93	90	88		92
7	99	93	90	87	98	93	89	87	92	89	86		91	88	86		90
8	97	91	87	85	96	91	87	85	90	87	85		89	86	84		88
9	95	89	85	83	94	89	85	83	88	85	83		87	84	83		87
10	93	87	84	81	92	87	83	81	86	83	81		86	83	81		85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3030810
5°	2551787
10°	1593825
15°	595872
20°	204534
25°	85239
30°	40158
35°	17989
40°	8502
45°	4373
50°	1603
55°	306
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4373 cd/sqm

TEST NUMBER: P1276718

CATALOG NUMBER: P3AS20R209835D010 E3D1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	964.0	48.2
10°-20°	794.1	39.7
20°-30°	180.5	9.0
30°-40°	45.9	2.3
40°-50°	11.6	0.6
50°-60°	1.5	0.1
60°-70°	0.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1938.6	97.0
0°-40°	1984.5	99.3
0°-60°	1997.6	100.0
0°-90°	1998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13822	
5°	11593	964
15°	2625	794
25°	352	180
35°	67	46
45°	14	12
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1276718

CATALOG NUMBER: P3AS20R209835D010 E3D1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	13821.6
1°	13704.4
2°	13359.1
3°	12863.8
4°	12256.1
5°	11592.8
6°	10853.8
7°	10038.3
8°	9086.8
9°	8143.9
10°	7158.0
11°	6108.9
12°	5061.3
13°	4173.9
14°	3325.5
15°	2624.8
16°	2071.7
17°	1634.2
18°	1313.2
19°	1067.9
20°	876.5
21°	732.8
22°	611.7
23°	508.6
24°	424.2
25°	352.3
27.5°	230.5
30°	158.6
32.5°	97.6
35°	67.2
37.5°	43.0
40°	29.7
42.5°	20.3
45°	14.1
47.5°	9.4
50°	4.7
52.5°	2.3
55°	0.8
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.0
70°	0.0
72.5°	0.0

TEST NUMBER: P1276718

CATALOG NUMBER: P3AS20R209835D010 E3D1WH

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)