

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276742

Luminaire Tested: P3AS20R259835D010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276742
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259835D010 E3D1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2155.0 lumens
Efficiency: N/A
Efficacy: 78.7 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276742

CATALOG NUMBER: P3AS20R259835D010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1276742

CATALOG NUMBER: P3AS20R259835D010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97	97	97
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94	94	94
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92	92	92
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89	89	89
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87	87	87
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85	85	85
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83	83	83
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81	81	81
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79	79	79
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77	77	77

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2360118
5°	2186325
10°	1691574
15°	807950
20°	266373
25°	112289
30°	43526
35°	18819
40°	6269
45°	2915
50°	1058
55°	612
60°	351
65°	415
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2915 cd/sqm

TEST NUMBER: P1276742

CATALOG NUMBER: P3AS20R259835D010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	873.1	40.5
10°-20°	993.0	46.1
20°-30°	230.7	10.7
30°-40°	48.4	2.2
40°-50°	7.8	0.4
50°-60°	1.3	0.1
60°-70°	0.7	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2096.8	97.3
0°-40°	2145.2	99.5
0°-60°	2154.4	100.0
0°-90°	2155.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2155.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10763	
5°	9932	873
15°	3559	993
25°	464	231
35°	70	48
45°	9	8
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1276742

CATALOG NUMBER: P3AS20R259835D010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10763.0
1°	10741.2
2°	10629.4
3°	10472.4
4°	10232.5
5°	9932.5
6°	9547.3
7°	9144.1
8°	8691.7
9°	8181.5
10°	7597.0
11°	6919.6
12°	6142.2
13°	5290.5
14°	4399.8
15°	3559.0
16°	2815.2
17°	2193.2
18°	1725.2
19°	1379.9
20°	1141.5
21°	954.0
22°	800.9
23°	668.8
24°	559.4
25°	464.1
27.5°	275.0
30°	171.9
32.5°	110.2
35°	70.3
37.5°	42.2
40°	21.9
42.5°	14.1
45°	9.4
47.5°	5.5
50°	3.1
52.5°	1.6
55°	1.6
57.5°	0.8
60°	0.8
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.0
72.5°	0.0

TEST NUMBER: P1276742

CATALOG NUMBER: P3AS20R259835D010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)