

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276754

Luminaire Tested: P3AS20R259835D010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276754
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R259835D010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1280.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276754

CATALOG NUMBER: P3AS20R259835D010 E3DLD1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1276754

CATALOG NUMBER: P3AS20R259835D010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	82	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	76	72		78
5	89	79	73	68	87	78	72	68	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	62		70	65	61		69
7	79	69	62	58	78	68	62	58	67	61	57		66	61	57		65
8	75	65	58	54	74	64	58	53	63	57	53		62	57	53		61
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57
10	68	57	51	47	67	57	51	47	56	50	47		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	304208
5°	296940
10°	275167
15°	245087
20°	210602
25°	179018
30°	147364
35°	114840
40°	82612
45°	52409
50°	31010
55°	21333
60°	19560
65°	18212
70°	16349
75°	14827
80°	14143
85°	12077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 52409 cd/sqm

TEST NUMBER: P1276754

CATALOG NUMBER: P3AS20R259835D010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	9.8
10°-20°	299.7	23.4
20°-30°	338.6	26.5
30°-40°	267.9	20.9
40°-50°	135.3	10.6
50°-60°	54.2	4.2
60°-70°	34.7	2.7
70°-80°	19.1	1.5
80°-90°	5.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.4	59.6
0°-40°	1031.3	80.6
0°-60°	1220.7	95.4
0°-90°	1280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1280.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1387	
5°	1349	125
15°	1080	300
25°	740	339
35°	429	268
45°	169	135
55°	56	54
65°	35	35
75°	18	19
85°	5	5
90°	0	

TEST NUMBER: P1276754

CATALOG NUMBER: P3AS20R259835D010 E3DLD1LI


CANDELA DISTRIBUTION (FULL):

0°	
0°	1387.3
1°	1387.3
2°	1382.5
3°	1374.6
4°	1363.4
5°	1349.0
6°	1331.5
7°	1310.8
8°	1288.4
9°	1262.9
10°	1235.8
11°	1205.5
12°	1176.8
13°	1143.3
14°	1111.4
15°	1079.6
17.5°	990.3
20°	902.5
22.5°	819.6
25°	739.9
27.5°	661.8
30°	582.0
32.5°	507.1
35°	429.0
37.5°	357.2
40°	288.6
42.5°	224.8
45°	169.0
47.5°	126.0
50°	90.9
52.5°	68.6
55°	55.8
57.5°	51.0
60°	44.6
62.5°	39.9
65°	35.1
67.5°	30.3
70°	25.5
72.5°	22.3
75°	17.5
77.5°	14.4
80°	11.2
82.5°	8.0
85°	4.8
87.5°	1.6



TEST NUMBER: P1276754
CATALOG NUMBER: P3AS20R259835D010 E3DLD1LI

CANDELA DISTRIBUTION (continued):



(END OF REPORT)