

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275789

Luminaire Tested: P3AS09R359835DE010 E3PH1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275789
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-5)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R359835DE010 E3PH1MW
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3PH1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 663.0 lumens
Efficiency: N/A
Efficacy: 60.3 lumens/watt
Spacing Criteria (0/90/45): 0.57 / 0.56 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275789
CATALOG NUMBER: P3AS09R359835DE010 E3PH1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1275789

CATALOG NUMBER: P3AS09R359835DE010 E3PH1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99	100	98	97	97	96	95	93
3	108	103	100	97	106	102	99	96	99	97	94	97	95	93	95	93	92	90
4	104	99	95	92	103	98	94	92	96	93	91	94	92	90	93	90	89	87
5	101	95	91	88	100	95	91	88	93	90	87	92	89	87	90	88	86	85
6	98	92	88	85	97	91	88	85	90	87	84	89	86	84	88	85	83	82
7	96	89	85	82	94	89	85	82	87	84	81	86	83	81	85	83	81	80
8	93	86	82	79	92	86	82	79	85	81	79	84	81	79	83	80	78	77
9	90	84	80	77	89	83	79	77	82	79	76	82	79	76	81	78	76	75
10	88	81	77	75	87	81	77	74	80	77	74	80	76	74	79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	478997	478997	478997
5°	470767	469754	468742
10°	431455	418474	408298
15°	308946	299094	295461
20°	143256	148180	153383
25°	33994	48366	50422
30°	9976	11419	12863
35°	2302	3667	3373
40°	487	973	658
45°	186	186	186
50°	205	0	205
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 52.5°

Luminance: 216 cd/sqm



TEST NUMBER: P1275789
 CATALOG NUMBER: P3AS09R359835DE010 E3PH1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.1	29.6
10°-20°	350.6	52.9
20°-30°	105.5	15.9
30°-40°	10.1	1.5
40°-50°	0.7	0.1
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	652.2	98.4
0°-40°	662.3	99.9
0°-60°	663.0	100.0
0°-90°	663.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	663.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2184	2184	2184	2184	2184	
5°	2139	2138	2134	2131	2130	198
15°	1361	1351	1318	1312	1302	359
25°	140	155	200	208	208	90
35°	9	11	14	15	13	8
45°	1	1	1	1	1	1
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P1275789

CATALOG NUMBER: P3AS09R359835DE010 E3PH1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2184.4	2184.4	2184.4	2184.4	2184.4
1°	2183.2	2183.2	2182.1	2182.1	2179.8
2°	2178.1	2178.6	2176.4	2175.8	2174.1
3°	2170.1	2168.4	2168.4	2167.2	2166.1
4°	2157.5	2154.1	2152.9	2153.5	2151.2
5°	2138.7	2138.1	2134.1	2131.2	2129.5
6°	2118.1	2114.1	2105.5	2098.1	2096.4
7°	2087.3	2078.7	2071.3	2055.9	2053.6
8°	2049.6	2035.9	2019.9	1998.2	1997.0
9°	2003.3	1981.1	1958.8	1929.7	1919.4
10°	1937.7	1917.1	1879.4	1853.7	1833.7
11°	1856.0	1830.3	1786.3	1755.5	1738.9
12°	1763.5	1739.5	1688.1	1660.1	1636.7
13°	1644.7	1624.7	1576.7	1545.9	1527.6
14°	1507.1	1492.2	1446.5	1432.8	1426.5
15°	1360.9	1350.6	1317.5	1311.8	1301.5
17.5°	1001.7	984.5	965.7	969.1	972.5
20°	613.9	637.9	635.0	647.6	657.3
22.5°	306.1	336.9	372.9	394.6	405.5
25°	140.5	154.8	199.9	208.4	208.4
27.5°	70.8	74.2	94.2	95.9	100.5
30°	39.4	42.3	45.1	50.3	50.8
32.5°	20.0	23.4	24.6	27.4	26.3
35°	8.6	11.4	13.7	14.8	12.6
37.5°	4.0	5.1	7.4	6.9	5.1
40°	1.7	2.3	3.4	2.9	2.3
42.5°	1.1	1.1	1.7	1.1	1.1
45°	0.6	0.6	0.6	0.6	0.6
47.5°	0.6	0.6	0.0	0.6	0.6
50°	0.6	0.0	0.0	0.0	0.6
52.5°	0.6	0.0	0.0	0.0	0.6
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P1275789
CATALOG NUMBER: P3AS09R359835DE010 E3PH1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)