

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275802

Luminaire Tested: P3AS09R409835DE010 E3D1WMH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R409835DE010 E3D1WMH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 799.1 lumens
Efficiency: N/A
Efficacy: 72.6 lumens/watt
Spacing Criteria (0/90/45): 0.7 / 0.7 / 0.6
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275802

CATALOG NUMBER: P3AS09R409835DE010 E3D1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275802

CATALOG NUMBER: P3AS09R409835DE010 E3D1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	115	112	110	109	112	110	109	107	106	105	104		103	102	101		99
2	111	107	104	101	109	105	102	100	102	100	98		99	97	96		96
3	107	102	98	95	105	100	97	94	98	95	93		96	93	91		93
4	103	97	93	90	101	96	92	89	94	91	88		92	89	87		90
5	99	93	89	85	98	92	88	85	91	87	84		89	86	84		88
6	96	89	85	81	95	89	84	81	87	83	81		86	83	80		85
7	93	86	81	78	92	85	81	78	84	80	77		83	80	77		82
8	90	83	78	75	89	82	78	75	81	77	75		80	77	74		79
9	87	80	75	72	86	79	75	72	78	75	72		78	74	72		77
10	84	77	72	70	83	77	72	69	76	72	69		75	72	69		74

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	407270
5°	404335
10°	393736
15°	351716
20°	233214
25°	87368
30°	23371
35°	9128
40°	3292
45°	1551
50°	478
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1551 cd/sqm

TEST NUMBER: P1275802

CATALOG NUMBER: P3AS09R409835DE010 E3D1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.3	21.7
10°-20°	410.5	51.4
20°-30°	186.2	23.3
30°-40°	24.1	3.0
40°-50°	4.2	0.5
50°-60°	0.5	0.1
60°-70°	0.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	770.0	96.4
0°-40°	794.2	99.4
0°-60°	798.9	100.0
0°-90°	799.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	799.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1857	
5°	1837	173
15°	1549	411
25°	361	186
35°	34	24
45°	5	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1275802

CATALOG NUMBER: P3AS09R409835DE010 E3D1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1857.3
1°	1856.2
2°	1853.4
3°	1849.2
4°	1843.9
5°	1836.9
6°	1828.8
7°	1818.7
8°	1806.4
9°	1789.6
10°	1768.3
11°	1743.5
12°	1710.2
13°	1669.0
14°	1615.3
15°	1549.3
16°	1465.1
17°	1369.2
18°	1254.0
19°	1132.3
20°	999.4
21°	866.6
22°	735.6
23°	605.3
24°	477.2
25°	361.1
26°	267.4
27°	195.8
28°	147.1
29°	114.4
30°	92.3
31°	76.4
32°	63.8
32.5°	58.2
33°	52.6
34°	42.8
35°	34.1
36°	26.9
37°	21.3
37.5°	19.0
38°	16.8
39°	14.0
40°	11.5
42.5°	7.6
45°	5.0

TEST NUMBER: P1275802

CATALOG NUMBER: P3AS09R409835DE010 E3D1WMH

CANDELA DISTRIBUTION (continued):

	0°
47.5°	3.1
50°	1.4
52.5°	0.6
55°	0.6
57.5°	0.3
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)