

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276756

Luminaire Tested: P3AS20R259835D010 E3DLD1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276756  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R259835D010 E3DLD1WH  
Description: 3in Adjustable LED luminaire with, R25 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1280.0 lumens  
Efficiency: N/A  
Efficacy: 46.7 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.85  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276756  
CATALOG NUMBER: P3AS20R259835D010 E3DLD1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276756  
 CATALOG NUMBER: P3AS20R259835D010 E3DLD1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	99	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	82	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70			70
5	89	79	73	68	87	78	72	68	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59			59
7	79	69	62	58	78	68	62	58	67	61	57	66	61	57	65	60	57	55			55
8	75	65	58	54	74	64	58	53	63	57	53	62	57	53	61	56	53	51			51
9	71	61	54	50	70	60	54	50	59	54	50	58	53	50	57	53	49	48			48
10	68	57	51	47	67	57	51	47	56	50	47	55	50	46	54	50	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	304208
5°	296940
10°	275167
15°	245087
20°	210602
25°	179018
30°	147364
35°	114840
40°	82612
45°	52409
50°	31010
55°	21333
60°	19560
65°	18212
70°	16349
75°	14827
80°	14143
85°	12077

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 52409 cd/sqm



TEST NUMBER: P1276756  
 CATALOG NUMBER: P3AS20R259835D010 E3DLD1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	125.1	9.8
10°-20°	299.7	23.4
20°-30°	338.6	26.5
30°-40°	267.9	20.9
40°-50°	135.3	10.6
50°-60°	54.2	4.2
60°-70°	34.7	2.7
70°-80°	19.1	1.5
80°-90°	5.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	763.4	59.6
0°-40°	1031.3	80.6
0°-60°	1220.7	95.4
0°-90°	1280.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1280.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1387	
5°	1349	125
15°	1080	300
25°	740	339
35°	429	268
45°	169	135
55°	56	54
65°	35	35
75°	18	19
85°	5	5
90°	0	



TEST NUMBER: P1276756  
CATALOG NUMBER: P3AS20R259835D010 E3DLD1WH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1387.3
1°	1387.3
2°	1382.5
3°	1374.6
4°	1363.4
5°	1349.0
6°	1331.5
7°	1310.8
8°	1288.4
9°	1262.9
10°	1235.8
11°	1205.5
12°	1176.8
13°	1143.3
14°	1111.4
15°	1079.6
17.5°	990.3
20°	902.5
22.5°	819.6
25°	739.9
27.5°	661.8
30°	582.0
32.5°	507.1
35°	429.0
37.5°	357.2
40°	288.6
42.5°	224.8
45°	169.0
47.5°	126.0
50°	90.9
52.5°	68.6
55°	55.8
57.5°	51.0
60°	44.6
62.5°	39.9
65°	35.1
67.5°	30.3
70°	25.5
72.5°	22.3
75°	17.5
77.5°	14.4
80°	11.2
82.5°	8.0
85°	4.8
87.5°	1.6



TEST NUMBER: P1276756  
CATALOG NUMBER: P3AS20R259835D010 E3DLD1WH

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)