

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275852

Luminaire Tested: P3AS09R509835DE010 E3D1H

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275852
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R509835DE010 E3D1H
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3D1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 793.0 lumens
Efficiency: N/A
Efficacy: 72.1 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275852

CATALOG NUMBER: P3AS09R509835DE010 E3D1H

Luminous Intensity Polar Plot



TEST NUMBER: P1275852

CATALOG NUMBER: P3AS09R509835DE010 E3D1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	110	108	106	105	104	102	102	101	99	98	97	97	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90		
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85		
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80		
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76		
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72		
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	68		
8	84	76	71	67	83	76	71	67	74	70	67	74	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	60	67	63	60	67	63	60	59		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	277127
5°	269733
10°	257421
15°	233032
20°	201618
25°	165372
30°	95002
35°	29500
40°	7929
45°	2791
50°	682
55°	229
60°	132
65°	156
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2791 cd/sqm

TEST NUMBER: P1275852

CATALOG NUMBER: P3AS09R509835DE010 E3D1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	114.8	14.5
10°-20°	284.4	35.9
20°-30°	298.9	37.7
30°-40°	85.6	10.8
40°-50°	8.4	1.1
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	698.2	88.0
0°-40°	783.7	98.8
0°-60°	792.8	100.0
0°-90°	793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1264	
5°	1225	115
15°	1026	284
25°	684	299
35°	110	86
45°	9	8
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1275852

CATALOG NUMBER: P3AS09R509835DE010 E3D1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1263.8
1°	1261.8
2°	1256.2
3°	1248.1
4°	1237.2
5°	1225.4
6°	1212.9
7°	1199.4
8°	1186.8
9°	1172.3
10°	1156.1
11°	1137.3
12°	1115.8
13°	1088.9
14°	1059.8
15°	1026.5
16°	991.3
17°	957.1
18°	922.2
19°	891.4
20°	864.0
21°	837.7
22°	807.7
23°	773.3
24°	733.0
25°	683.5
26°	629.8
27°	569.9
28°	510.3
29°	446.0
30°	375.2
31°	308.9
32°	247.9
32.5°	221.3
33°	194.4
34°	149.1
35°	110.2
36°	80.9
37°	60.2
37.5°	52.0
38°	45.0
39°	35.0
40°	27.7
42.5°	15.7
45°	9.0



TEST NUMBER: P1275852

CATALOG NUMBER: P3AS09R509835DE010 E3D1H

CANDELA DISTRIBUTION (continued):

	0°
47.5°	5.0
50°	2.0
52.5°	0.8
55°	0.6
57.5°	0.6
60°	0.3
62.5°	0.3
65°	0.3
67.5°	0.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)