

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276769

Luminaire Tested: P3AS20R309835D010 E3CB1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276769
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-16)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309835D010 E3CB1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3CB1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2029.1 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.47
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276769
CATALOG NUMBER: P3AS20R309835D010 E3CB1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1276769

CATALOG NUMBER: P3AS20R309835D010 E3CB1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	98	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	98	96	95	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	95	94	92	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	94	92	93	91	89	91
4	105	100	96	93	103	99	95	92	97	94	91	95	92	90	93	91	89	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	87	91	88	87	85
6	99	93	89	86	98	92	88	86	91	88	85	90	87	85	89	86	84	89	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	84	82	80	79
9	91	85	81	78	90	84	81	78	84	80	78	83	80	78	82	79	77	82	79	77	77
10	89	83	79	76	88	82	78	76	82	78	76	81	78	76	80	77	75	80	77	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1652280
5°	1621061
10°	1435044
15°	909199
20°	345130
25°	102175
30°	40361
35°	12367
40°	5467
45°	1985
50°	1637
55°	1223
60°	1403
65°	1660
70°	1026
75°	1356
80°	2020
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 80°
 Luminance: 2020 cd/sqm



TEST NUMBER: P1276769
 CATALOG NUMBER: P3AS20R309835D010 E3CB1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	677.0	33.4
10°-20°	1055.1	52.0
20°-30°	245.0	12.1
30°-40°	38.0	1.9
40°-50°	6.5	0.3
50°-60°	3.0	0.1
60°-70°	2.6	0.1
70°-80°	1.7	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1977.1	97.4
0°-40°	2015.0	99.3
0°-60°	2024.6	99.8
0°-90°	2029.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2029.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7535	
5°	7364	677
15°	4005	1055
25°	422	245
35°	46	38
45°	6	7
55°	3	3
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1276769
CATALOG NUMBER: P3AS20R309835D010 E3CB1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	7535.0
1°	7530.3
2°	7509.5
3°	7474.5
4°	7429.9
5°	7364.5
6°	7283.2
7°	7162.1
8°	6996.4
9°	6752.5
10°	6444.9
11°	6048.1
12°	5600.3
13°	5103.0
14°	4556.4
15°	4005.0
17.5°	2620.1
20°	1479.0
22.5°	755.4
25°	422.3
27.5°	259.8
30°	159.4
32.5°	86.1
35°	46.2
37.5°	30.3
40°	19.1
42.5°	11.2
45°	6.4
47.5°	4.8
50°	4.8
52.5°	3.2
55°	3.2
57.5°	3.2
60°	3.2
62.5°	3.2
65°	3.2
67.5°	1.6
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P1276769
CATALOG NUMBER: P3AS20R309835D010 E3CB1MW

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)