

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276778

Luminaire Tested: P3AS20R309835D010 E3DL1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276778
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R309835D010 E3DL1GPH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 827.0 lumens
Efficiency: N/A
Efficacy: 30.2 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276778
CATALOG NUMBER: P3AS20R309835D010 E3DL1GPH

Luminous Intensity Polar Plot





TEST NUMBER: P1276778

CATALOG NUMBER: P3AS20R309835D010 E3DL1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	95	95	95
2	110	105	102	99	107	104	101	98	101	98	96	98	96	94	95	93	92	90	90	90	90
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86	86	86	86
4	101	95	90	87	99	94	89	86	92	88	85	90	87	84	88	85	83	82	82	82	82
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78	78	78	78
6	94	86	81	78	92	85	81	77	84	80	77	83	79	76	81	78	76	75	75	75	75
7	90	82	77	74	89	82	77	74	81	76	73	80	76	73	79	75	73	71	71	71	71
8	87	79	74	71	86	79	74	71	78	73	70	77	73	70	76	72	70	69	69	69	69
9	84	76	71	68	83	75	71	68	75	70	67	74	70	67	73	70	67	66	66	66	66
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	63	63	63	63

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	482571
5°	459321
10°	386343
15°	278617
20°	172822
25°	98280
30°	54591
35°	29687
40°	15658
45°	8466
50°	4537
55°	2982
60°	2719
65°	2854
70°	2500
75°	1949
80°	2020
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8466 cd/sqm



TEST NUMBER: P1276778
 CATALOG NUMBER: P3AS20R309835D010 E3DL1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.9	22.7
10°-20°	334.0	40.4
20°-30°	193.0	23.3
30°-40°	73.3	8.9
40°-50°	22.5	2.7
50°-60°	7.6	0.9
60°-70°	5.1	0.6
70°-80°	2.8	0.3
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.9	86.5
0°-40°	788.2	95.3
0°-60°	818.2	98.9
0°-90°	827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2201	
5°	2087	188
15°	1227	334
25°	406	193
35°	111	73
45°	27	22
55°	8	8
65°	6	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1276778
CATALOG NUMBER: P3AS20R309835D010 E3DL1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2200.7
1°	2199.2
2°	2185.9
3°	2160.9
4°	2129.6
5°	2086.7
6°	2032.0
7°	1971.1
8°	1903.1
9°	1821.8
10°	1735.1
11°	1641.4
12°	1542.2
13°	1438.3
14°	1332.8
15°	1227.3
17.5°	968.0
20°	740.6
22.5°	549.2
25°	406.2
27.5°	295.3
30°	215.6
32.5°	155.5
35°	110.9
37.5°	77.3
40°	54.7
42.5°	38.3
45°	27.3
47.5°	18.7
50°	13.3
52.5°	9.4
55°	7.8
57.5°	7.0
60°	6.2
62.5°	5.5
65°	5.5
67.5°	4.7
70°	3.9
72.5°	3.1
75°	2.3
77.5°	2.3
80°	1.6
82.5°	1.6
85°	0.8
87.5°	0.0



TEST NUMBER: P1276778
CATALOG NUMBER: P3AS20R309835D010 E3DL1GPH

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)