

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275917

Luminaire Tested: P3AS09R609835DE010 E3DL1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275917
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609835DE010 E3DL1LI
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 600.0 lumens
Efficiency: N/A
Efficacy: 54.5 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275917

CATALOG NUMBER: P3AS09R609835DE010 E3DL1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1275917

CATALOG NUMBER: P3AS09R609835DE010 E3DL1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		0
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		85
3	101	95	89	85	99	93	88	84	91	86	83		88	85	82		79
4	96	88	82	78	94	87	81	77	85	80	76		83	79	75		73
5	91	82	76	71	89	81	75	71	79	74	70		78	73	70		68
6	86	77	70	66	84	76	70	66	74	69	65		73	68	65		63
7	82	72	66	61	80	71	65	61	70	65	61		69	64	60		59
8	77	68	61	57	76	67	61	57	66	60	57		65	60	56		55
9	74	64	57	53	72	63	57	53	62	57	53		61	56	53		51
10	70	60	54	50	69	60	54	50	59	53	50		58	53	50		48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141677
5°	140347
10°	136248
15°	127651
20°	112990
25°	94505
30°	74062
35°	53726
40°	35753
45°	22297
50°	12076
55°	3479
60°	3245
65°	2958
70°	2949
75°	2881
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22297 cd/sqm

TEST NUMBER: P1275917

CATALOG NUMBER: P3AS09R609835DE010 E3DL1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.0	10.0
10°-20°	156.0	26.0
20°-30°	177.8	29.6
30°-40°	126.1	21.0
40°-50°	57.2	9.5
50°-60°	12.1	2.0
60°-70°	5.8	1.0
70°-80°	3.6	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	393.8	65.6
0°-40°	519.9	86.7
0°-60°	589.3	98.2
0°-90°	600.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	600.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	646	
5°	638	60
15°	562	156
25°	391	178
35°	201	126
45°	72	57
55°	9	12
65°	6	6
75°	3	4
85°	1	1
90°	0	

TEST NUMBER: P1275917

CATALOG NUMBER: P3AS09R609835DE010 E3DL1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	646.1
2.5°	643.8
5°	637.6
7.5°	626.7
10°	611.9
12.5°	590.8
15°	562.3
17.5°	526.4
20°	484.2
22.5°	438.5
25°	390.6
27.5°	341.6
30°	292.5
32.5°	245.8
35°	200.7
37.5°	160.8
40°	124.9
42.5°	94.7
45°	71.9
47.5°	53.6
50°	35.4
52.5°	16.5
55°	9.1
57.5°	8.0
60°	7.4
62.5°	6.8
65°	5.7
67.5°	5.1
70°	4.6
72.5°	4.0
75°	3.4
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)