

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275921

Luminaire Tested: P3AS09R609835DE010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275921
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-38)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R609835DE010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 230.9 lumens
Efficiency: N/A
Efficacy: 21.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275921

CATALOG NUMBER: P3AS09R609835DE010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1275921

CATALOG NUMBER: P3AS09R609835DE010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	98	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	91	82	76	71	80	75	71		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41005
5°	40546
10°	39144
15°	36981
20°	34093
25°	30873
30°	27397
35°	23423
40°	18606
45°	13118
50°	7846
55°	3976
60°	3815
65°	3476
70°	3206
75°	3050
80°	2778
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13118 cd/sqm

TEST NUMBER: P1275921

CATALOG NUMBER: P3AS09R609835DE010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.3	7.5
10°-20°	45.5	19.7
20°-30°	58.5	25.3
30°-40°	54.2	23.5
40°-50°	33.0	14.3
50°-60°	11.0	4.8
60°-70°	6.7	2.9
70°-80°	3.7	1.6
80°-90°	1.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	121.3	52.5
0°-40°	175.5	76.0
0°-60°	219.5	95.0
0°-90°	230.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	230.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	187	
5°	184	17
15°	163	46
25°	128	58
35°	88	54
45°	42	33
55°	10	11
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1275921

CATALOG NUMBER: P3AS09R609835DE010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	187.0
2.5°	186.2
5°	184.2
7.5°	180.6
10°	175.8
12.5°	169.9
15°	162.9
17.5°	154.8
20°	146.1
22.5°	136.8
25°	127.6
27.5°	118.0
30°	108.2
32.5°	98.4
35°	87.5
37.5°	76.0
40°	65.0
42.5°	53.5
45°	42.3
47.5°	32.8
50°	23.0
52.5°	13.7
55°	10.4
57.5°	9.5
60°	8.7
62.5°	7.6
65°	6.7
67.5°	5.9
70°	5.0
72.5°	4.2
75°	3.6
77.5°	2.8
80°	2.2
82.5°	1.4
85°	0.8
87.5°	0.6
90°	0.0

(END OF REPORT)