

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275955

Luminaire Tested: P3AS09R659835DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R659835DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 449.0 lumens
Efficiency: N/A
Efficacy: 40.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275955

CATALOG NUMBER: P3AS09R659835DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1275955

CATALOG NUMBER: P3AS09R659835DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88
3	99	91	85	80	96	89	84	79	87	82	78		84	80	77		82
4	92	83	77	72	90	82	76	71	80	75	70		78	73	70		76
5	87	77	70	65	85	76	69	65	74	68	64		72	67	63		71
6	82	71	64	59	80	70	64	59	69	63	58		67	62	58		66
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61
8	72	61	55	50	71	61	54	50	60	54	49		59	53	49		58
9	68	57	51	46	67	57	50	46	56	50	46		55	49	46		54
10	65	54	47	43	64	53	47	43	52	47	43		52	46	42		51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79906
5°	78824
10°	76173
15°	71851
20°	66272
25°	60149
30°	53274
35°	45347
40°	36068
45°	25460
50°	14771
55°	8067
60°	7499
65°	6797
70°	6219
75°	5761
80°	5051
85°	4277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 25460 cd/sqm

TEST NUMBER: P1275955

CATALOG NUMBER: P3AS09R659835DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	33.7	7.5
10°-20°	88.5	19.7
20°-30°	113.8	25.3
30°-40°	105.3	23.4
40°-50°	63.5	14.2
50°-60°	21.7	4.8
60°-70°	13.0	2.9
70°-80°	7.4	1.6
80°-90°	2.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	236.0	52.6
0°-40°	341.3	76.0
0°-60°	426.5	95.0
0°-90°	449.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	449.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	364	
5°	358	34
15°	316	89
25°	249	114
35°	169	105
45°	82	64
55°	21	22
65°	13	13
75°	7	7
85°	2	2
90°	0	

TEST NUMBER: P1275955

CATALOG NUMBER: P3AS09R659835DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	364.4
2.5°	362.7
5°	358.1
7.5°	351.3
10°	342.1
12.5°	330.7
15°	316.5
17.5°	301.1
20°	284.0
22.5°	266.3
25°	248.6
27.5°	229.8
30°	210.4
32.5°	191.0
35°	169.4
37.5°	148.3
40°	126.0
42.5°	103.8
45°	82.1
47.5°	62.2
50°	43.3
52.5°	27.4
55°	21.1
57.5°	18.8
60°	17.1
62.5°	14.8
65°	13.1
67.5°	11.4
70°	9.7
72.5°	8.6
75°	6.8
77.5°	5.7
80°	4.0
82.5°	2.9
85°	1.7
87.5°	1.1
90°	0.0

(END OF REPORT)