

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276830

Luminaire Tested: P3AS20R409835D010 E3CD1MB

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276830  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-24)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R409835D010 E3CD1MB  
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3CD1MB TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2239.0 lumens  
Efficiency: N/A  
Efficacy: 81.7 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.59  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276830  
CATALOG NUMBER: P3AS20R409835D010 E3CD1MB

### Luminous Intensity Polar Plot





TEST NUMBER: P1276830  
 CATALOG NUMBER: P3AS20R409835D010 E3CD1MB

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	115	112	110	109	112	110	109	107	106	105	104	103	102	101	99	98	98	96			96
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	96	95	94	92			92
3	107	102	98	95	105	100	97	94	98	95	93	96	93	91	94	92	90	89			89
4	103	97	93	90	102	96	92	89	94	91	88	92	90	87	91	88	86	85			85
5	100	93	89	86	98	92	88	85	91	87	85	89	86	84	88	85	83	82			82
6	96	90	85	82	95	89	85	82	88	84	81	86	83	81	85	82	80	79			79
7	93	86	82	79	92	86	81	78	85	81	78	83	80	78	82	79	77	76			76
8	90	83	79	76	89	83	78	75	82	78	75	81	77	75	80	77	75	73			73
9	87	80	76	73	87	80	76	73	79	75	72	78	75	72	77	74	72	71			71
10	85	77	73	70	84	77	73	70	76	73	70	76	72	70	75	72	70	69			69

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1178897
5°	1173231
10°	1134982
15°	1004160
20°	655164
25°	232078
30°	49223
35°	16195
40°	5925
45°	1985
50°	1637
55°	1835
60°	1403
65°	1660
70°	1026
75°	1356
80°	2020
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 82.5°  
 Luminance: 2688 cd/sqm



TEST NUMBER: P1276830  
 CATALOG NUMBER: P3AS20R409835D010 E3CD1MB

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	501.5	22.4
10°-20°	1167.9	52.2
20°-30°	506.8	22.6
30°-40°	46.7	2.1
40°-50°	6.6	0.3
50°-60°	4.1	0.2
60°-70°	3.0	0.1
70°-80°	1.7	0.1
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2176.3	97.2
0°-40°	2223.0	99.3
0°-60°	2233.7	99.8
0°-90°	2239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2239.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5376	
5°	5330	502
15°	4423	1168
25°	959	507
35°	60	47
45°	6	7
55°	5	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1276830  
CATALOG NUMBER: P3AS20R409835D010 E3CD1MB

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5376.2
2.5°	5369.8
5°	5330.0
7.5°	5245.5
10°	5097.3
12.5°	4847.2
15°	4423.3
17.5°	3720.6
20°	2807.6
22.5°	1822.9
25°	959.2
27.5°	412.7
30°	194.4
32.5°	105.2
35°	60.5
37.5°	36.6
40°	20.7
42.5°	11.2
45°	6.4
47.5°	4.8
50°	4.8
52.5°	4.8
55°	4.8
57.5°	4.8
60°	3.2
62.5°	3.2
65°	3.2
67.5°	3.2
70°	1.6
72.5°	1.6
75°	1.6
77.5°	1.6
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)