

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1275980

Luminaire Tested: P3AS09R709835DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1275980
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R709835DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 410.0 lumens
Efficiency: N/A
Efficacy: 37.3 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1275980
CATALOG NUMBER: P3AS09R709835DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1275980
 CATALOG NUMBER: P3AS09R709835DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	104	110	107	105	103	103	101	100	100	98	97	96	95	94	92				92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84				84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77				77
4	95	86	80	76	93	85	80	75	83	78	74	81	77	73	79	76	73	71				71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65				65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	65	62	61				61
7	80	70	64	59	79	69	63	59	68	62	58	67	62	58	66	61	58	56				56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49				49
10	69	58	52	48	67	58	52	48	57	51	48	56	51	48	55	51	47	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	96177
5°	94409
10°	89021
15°	80795
20°	70659
25°	59616
30°	48818
35°	37852
40°	27108
45°	17149
50°	8563
55°	5238
60°	4517
65°	4151
70°	3654
75°	3389
80°	2904
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17149 cd/sqm



TEST NUMBER: P1275980
 CATALOG NUMBER: P3AS09R709835DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.0	9.8
10°-20°	99.0	24.2
20°-30°	112.8	27.5
30°-40°	88.2	21.5
40°-50°	43.3	10.6
50°-60°	13.3	3.3
60°-70°	7.9	1.9
70°-80°	4.2	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.8	61.4
0°-40°	340.0	82.9
0°-60°	396.7	96.7
0°-90°	410.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	410.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	439	
5°	429	40
15°	356	99
25°	246	113
35°	141	88
45°	55	43
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1275980
CATALOG NUMBER: P3AS09R709835DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	438.6
2.5°	436.3
5°	428.9
7.5°	416.9
10°	399.8
12.5°	379.8
15°	355.9
17.5°	330.2
20°	302.8
22.5°	274.3
25°	246.4
27.5°	219.0
30°	192.8
32.5°	166.5
35°	141.4
37.5°	117.5
40°	94.7
42.5°	73.6
45°	55.3
47.5°	38.8
50°	25.1
52.5°	16.5
55°	13.7
57.5°	12.0
60°	10.3
62.5°	9.1
65°	8.0
67.5°	6.8
70°	5.7
72.5°	4.6
75°	4.0
77.5°	3.4
80°	2.3
82.5°	1.7
85°	1.1
87.5°	0.6
90°	0.0

(END OF REPORT)