

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276844

Luminaire Tested: P3AS20R409835D010 E3DLD1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276844
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409835D010 E3DLD1GPH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 698.0 lumens
Efficiency: N/A
Efficacy: 25.5 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276844

CATALOG NUMBER: P3AS20R409835D010 E3DLD1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276844

CATALOG NUMBER: P3AS20R409835D010 E3DLD1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	156676
5°	153841
10°	145021
15°	131715
20°	115720
25°	98812
30°	81861
35°	63122
40°	44941
45°	30267
50°	16511
55°	11660
60°	10964
65°	10118
70°	9040
75°	8642
80°	6945
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30267 cd/sqm

TEST NUMBER: P1276844

CATALOG NUMBER: P3AS20R409835D010 E3DLD1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	9.3
10°-20°	161.6	23.2
20°-30°	186.9	26.8
30°-40°	147.3	21.1
40°-50°	75.6	10.8
50°-60°	28.9	4.1
60°-70°	19.1	2.7
70°-80°	10.4	1.5
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	413.7	59.3
0°-40°	560.9	80.4
0°-60°	665.4	95.3
0°-90°	698.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	698.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	714	
5°	699	65
15°	580	162
25°	408	187
35°	236	147
45°	98	76
55°	30	29
65°	20	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1276844

CATALOG NUMBER: P3AS20R409835D010 E3DLD1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	714.5
2.5°	710.6
5°	698.9
7.5°	678.6
10°	651.3
12.5°	619.3
15°	580.2
17.5°	539.6
20°	495.9
22.5°	451.4
25°	408.4
27.5°	365.5
30°	323.3
32.5°	280.4
35°	235.8
37.5°	194.5
40°	157.0
42.5°	124.9
45°	97.6
47.5°	71.1
50°	48.4
52.5°	35.1
55°	30.5
57.5°	27.3
60°	25.0
62.5°	21.9
65°	19.5
67.5°	16.4
70°	14.1
72.5°	11.7
75°	10.2
77.5°	7.8
80°	5.5
82.5°	4.7
85°	2.3
87.5°	1.6
90°	0.0

(END OF REPORT)