

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276023

Luminaire Tested: P3AS13R209835DE010 E3CD1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276023
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R209835DE010 E3CD1MMS
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 956.1 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276023

CATALOG NUMBER: P3AS13R209835DE010 E3CD1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1276023

CATALOG NUMBER: P3AS13R209835DE010 E3CD1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	116	114	112	110	113	112	110	109	108	106	105	104	103	102	101	100	99	98		
2	112	109	106	104	110	108	105	103	104	103	101	102	100	99	99	98	97	95		
3	109	105	102	100	108	104	101	99	102	99	97	99	98	96	97	96	95	93		
4	107	102	99	96	105	101	98	96	99	97	94	97	95	93	96	94	92	91		
5	104	99	96	93	103	98	95	93	97	94	92	95	93	91	94	92	91	90		
6	102	97	93	91	101	96	93	90	95	92	90	94	91	89	93	90	89	88		
7	100	94	91	88	99	94	91	88	93	90	88	92	89	87	91	89	87	86		
8	98	92	89	86	97	92	89	86	91	88	86	90	88	86	89	87	85	85		
9	96	90	87	85	95	90	87	85	89	86	84	89	86	84	88	86	84	83		
10	94	89	85	83	93	88	85	83	88	85	83	87	84	83	86	84	82	82		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1484771
5°	1288727
10°	796311
15°	276574
20°	84941
25°	30026
30°	11116
35°	4444
40°	2376
45°	930
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 930 cd/sqm

TEST NUMBER: P1276023

CATALOG NUMBER: P3AS13R209835DE010 E3CD1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	485.9	50.8
10°-20°	385.5	40.3
20°-30°	66.8	7.0
30°-40°	12.1	1.3
40°-50°	2.8	0.3
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.2	98.1
0°-40°	950.3	99.4
0°-60°	954.4	99.8
0°-90°	956.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	956.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6771	
5°	5855	486
15°	1218	386
25°	124	67
35°	17	12
45°	3	3
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1276023

CATALOG NUMBER: P3AS13R209835DE010 E3CD1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	6771.1
1°	6738.6
2°	6609.9
3°	6403.4
4°	6161.2
5°	5854.7
6°	5503.6
7°	5095.0
8°	4629.6
9°	4106.7
10°	3576.3
12.5°	2255.8
15°	1218.3
17.5°	650.8
20°	364.0
22.5°	208.1
25°	124.1
27.5°	75.7
30°	43.9
32.5°	25.7
35°	16.6
37.5°	11.4
40°	8.3
42.5°	5.3
45°	3.0
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)