

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276847

Luminaire Tested: P3AS20R409835D010 E3DLD1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276847
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409835D010 E3DLD1MW
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1424.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276847
CATALOG NUMBER: P3AS20R409835D010 E3DLD1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1276847

CATALOG NUMBER: P3AS20R409835D010 E3DLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319667
5°	313867
10°	295853
15°	268719
20°	236084
25°	201592
30°	167013
35°	128787
40°	91657
45°	61743
50°	33705
55°	23741
60°	22367
65°	20651
70°	18401
75°	17538
80°	14143
85°	12077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 61743 cd/sqm



TEST NUMBER: P1276847
 CATALOG NUMBER: P3AS20R409835D010 E3DLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	9.3
10°-20°	329.7	23.2
20°-30°	381.2	26.8
30°-40°	300.4	21.1
40°-50°	154.2	10.8
50°-60°	59.0	4.1
60°-70°	39.0	2.7
70°-80°	21.2	1.5
80°-90°	6.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.9	59.3
0°-40°	1144.3	80.4
0°-60°	1357.5	95.3
0°-90°	1424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1458	
5°	1426	133
15°	1184	330
25°	833	381
35°	481	300
45°	199	154
55°	62	59
65°	40	39
75°	21	21
85°	5	6
90°	0	



TEST NUMBER: P1276847

CATALOG NUMBER: P3AS20R409835D010 E3DLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1457.8
2.5°	1449.8
5°	1425.9
7.5°	1384.5
10°	1328.7
12.5°	1263.4
15°	1183.7
17.5°	1100.9
20°	1011.7
22.5°	920.9
25°	833.2
27.5°	745.6
30°	659.6
32.5°	572.0
35°	481.1
37.5°	396.7
40°	320.2
42.5°	254.9
45°	199.1
47.5°	145.0
50°	98.8
52.5°	71.7
55°	62.1
57.5°	55.8
60°	51.0
62.5°	44.6
65°	39.8
67.5°	33.5
70°	28.7
72.5°	23.9
75°	20.7
77.5°	15.9
80°	11.2
82.5°	9.6
85°	4.8
87.5°	3.2
90°	0.0

(END OF REPORT)