

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276848

Luminaire Tested: P3AS20R409835D010 E3DLD1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276848
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R409835D010 E3DLD1WH
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1424.0 lumens
Efficiency: N/A
Efficacy: 52.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276848

CATALOG NUMBER: P3AS20R409835D010 E3DLD1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276848

CATALOG NUMBER: P3AS20R409835D010 E3DLD1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	319667
5°	313867
10°	295853
15°	268719
20°	236084
25°	201592
30°	167013
35°	128787
40°	91657
45°	61743
50°	33705
55°	23741
60°	22367
65°	20651
70°	18401
75°	17538
80°	14143
85°	12077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 61743 cd/sqm

TEST NUMBER: P1276848

CATALOG NUMBER: P3AS20R409835D010 E3DLD1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.0	9.3
10°-20°	329.7	23.2
20°-30°	381.2	26.8
30°-40°	300.4	21.1
40°-50°	154.2	10.8
50°-60°	59.0	4.1
60°-70°	39.0	2.7
70°-80°	21.2	1.5
80°-90°	6.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	843.9	59.3
0°-40°	1144.3	80.4
0°-60°	1357.5	95.3
0°-90°	1424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1424.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1458	
5°	1426	133
15°	1184	330
25°	833	381
35°	481	300
45°	199	154
55°	62	59
65°	40	39
75°	21	21
85°	5	6
90°	0	

TEST NUMBER: P1276848

CATALOG NUMBER: P3AS20R409835D010 E3DLD1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1457.8
2.5°	1449.8
5°	1425.9
7.5°	1384.5
10°	1328.7
12.5°	1263.4
15°	1183.7
17.5°	1100.9
20°	1011.7
22.5°	920.9
25°	833.2
27.5°	745.6
30°	659.6
32.5°	572.0
35°	481.1
37.5°	396.7
40°	320.2
42.5°	254.9
45°	199.1
47.5°	145.0
50°	98.8
52.5°	71.7
55°	62.1
57.5°	55.8
60°	51.0
62.5°	44.6
65°	39.8
67.5°	33.5
70°	28.7
72.5°	23.9
75°	20.7
77.5°	15.9
80°	11.2
82.5°	9.6
85°	4.8
87.5°	3.2
90°	0.0

(END OF REPORT)