

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276030

Luminaire Tested: P3AS13R209835DE010 E3DL1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276030  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R209835DE010 E3DL1GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 3500K CCT AND, 98CRI , E3DL1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 384.0 lumens  
Efficiency: N/A  
Efficacy: 26.5 lumens/watt  
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276030  
CATALOG NUMBER: P3AS13R209835DE010 E3DL1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276030

CATALOG NUMBER: P3AS13R209835DE010 E3DL1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	97	93	91	94	92	89	92	90	88	87		
4	102	96	91	88	100	95	90	87	92	89	86	91	88	85	89	86	84	83		
5	98	91	87	83	97	90	86	83	89	85	82	87	84	81	86	83	81	79		
6	95	87	83	79	93	87	82	79	85	81	78	84	81	78	83	80	77	76		
7	91	84	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	73		
8	88	81	76	73	87	80	76	73	79	75	72	78	75	72	78	74	72	71		
9	85	78	73	70	85	77	73	70	77	73	70	76	72	69	75	72	69	68		
10	83	75	71	68	82	75	70	67	74	70	67	73	70	67	73	69	67	66		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	295437
5°	268566
10°	198482
15°	122793
20°	70123
25°	40018
30°	22459
35°	12207
40°	6698
45°	3690
50°	2149
55°	1567
60°	1447
65°	1349
70°	1218
75°	1271
80°	884
85°	1006

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3690 cd/sqm



TEST NUMBER: P1276030  
 CATALOG NUMBER: P3AS13R209835DE010 E3DL1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.7	27.5
10°-20°	150.8	39.3
20°-30°	78.7	20.5
30°-40°	30.4	7.9
40°-50°	9.9	2.6
50°-60°	3.9	1.0
60°-70°	2.6	0.7
70°-80°	1.5	0.4
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.2	87.3
0°-40°	365.6	95.2
0°-60°	379.4	98.8
0°-90°	384.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	384.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1347	
5°	1220	106
15°	541	151
25°	165	79
35°	46	30
45°	12	10
55°	4	4
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1276030  
CATALOG NUMBER: P3AS13R209835DE010 E3DL1GPH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1347.3
1°	1344.7
2°	1328.8
3°	1304.3
4°	1266.5
5°	1220.1
6°	1165.2
7°	1104.4
8°	1033.9
9°	965.2
10°	891.4
12.5°	708.5
15°	540.9
17.5°	404.7
20°	300.5
22.5°	222.6
25°	165.4
27.5°	122.0
30°	88.7
32.5°	64.2
35°	45.6
37.5°	33.0
40°	23.4
42.5°	16.7
45°	11.9
47.5°	8.5
50°	6.3
52.5°	4.8
55°	4.1
57.5°	3.7
60°	3.3
62.5°	3.0
65°	2.6
67.5°	2.2
70°	1.9
72.5°	1.9
75°	1.5
77.5°	1.1
80°	0.7
82.5°	0.7
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)