

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276850

Luminaire Tested: P3AS20R409835D010 E3DLP1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276850  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R409835D010 E3DLP1GPH  
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 574.0 lumens  
Efficiency: N/A  
Efficacy: 20.9 lumens/watt  
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276850  
CATALOG NUMBER: P3AS20R409835D010 E3DLP1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276850  
 CATALOG NUMBER: P3AS20R409835D010 E3DLP1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			
2	107	102	98	95	105	101	97	93	97	94	91	94	92	89	92	89	88	86			
3	102	95	90	86	100	94	89	85	91	87	84	89	85	83	86	84	81	80			
4	97	89	83	79	95	88	83	79	86	81	78	84	80	77	82	79	76	74			
5	92	83	77	73	90	82	77	73	81	76	72	79	75	71	77	74	71	69			
6	87	78	72	68	86	78	72	68	76	71	67	75	70	67	73	69	66	65			
7	83	74	68	64	82	73	68	63	72	67	63	71	66	63	70	66	62	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	178736
5°	175104
10°	163034
15°	142112
20°	114530
25°	85844
30°	60338
35°	39538
40°	23931
45°	14296
50°	8529
55°	6881
60°	6184
65°	5292
70°	5001
75°	3982
80°	3915
85°	4026

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14296 cd/sqm



TEST NUMBER: P1276850  
 CATALOG NUMBER: P3AS20R409835D010 E3DLP1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.9	12.9
10°-20°	172.4	30.0
20°-30°	162.5	28.3
30°-40°	94.0	16.4
40°-50°	37.4	6.5
50°-60°	16.6	2.9
60°-70°	10.2	1.8
70°-80°	5.4	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.7	71.2
0°-40°	502.7	87.6
0°-60°	556.7	97.0
0°-90°	574.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	574.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	815	
5°	796	74
15°	626	172
25°	355	162
35°	148	94
45°	46	37
55°	18	17
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1276850  
CATALOG NUMBER: P3AS20R409835D010 E3DLP1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	815.1
2.5°	810.4
5°	795.5
7.5°	768.2
10°	732.2
12.5°	683.8
15°	626.0
17.5°	561.1
20°	490.8
22.5°	420.4
25°	354.8
27.5°	293.8
30°	238.3
32.5°	189.9
35°	147.7
37.5°	111.8
40°	83.6
42.5°	62.5
45°	46.1
47.5°	33.6
50°	25.0
52.5°	20.3
55°	18.0
57.5°	16.4
60°	14.1
62.5°	11.7
65°	10.2
67.5°	8.6
70°	7.8
72.5°	6.3
75°	4.7
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)