

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276093

Luminaire Tested: P3AS13R309835DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309835DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 802.0 lumens
Efficiency: N/A
Efficacy: 55.3 lumens/watt
Spacing Criteria (0/90/45): 0.54 / 0.54 / 0.54
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276093

CATALOG NUMBER: P3AS13R309835DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1276093

CATALOG NUMBER: P3AS13R309835DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	85	81	77	84	80	77		83	79	76		81
7	90	82	77	74	89	82	77	74	81	76	73		80	76	73		79
8	87	79	74	71	86	79	74	71	78	73	70		77	73	70		76
9	84	76	71	68	83	75	71	68	75	70	67		74	70	67		73
10	81	73	68	65	80	73	68	65	72	68	65		71	67	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	467989
5°	445431
10°	374676
15°	270195
20°	167595
25°	95328
30°	52945
35°	28804
40°	15171
45°	8218
50°	4401
55°	2906
60°	2675
65°	2750
70°	2436
75°	1949
80°	1894
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8218 cd/sqm

TEST NUMBER: P1276093

CATALOG NUMBER: P3AS13R309835DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.2	22.7
10°-20°	323.9	40.4
20°-30°	187.2	23.3
30°-40°	71.0	8.9
40°-50°	21.8	2.7
50°-60°	7.4	0.9
60°-70°	5.0	0.6
70°-80°	2.7	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	693.3	86.4
0°-40°	764.4	95.3
0°-60°	793.5	98.9
0°-90°	802.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	802.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2134	
5°	2024	182
15°	1190	324
25°	394	187
35°	108	71
45°	26	22
55°	8	7
65°	5	5
75°	2	3
85°	1	1
90°	0	

TEST NUMBER: P1276093

CATALOG NUMBER: P3AS13R309835DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2134.2
1°	2132.7
2°	2119.8
3°	2095.6
4°	2065.3
5°	2023.6
6°	1970.6
7°	1911.5
8°	1845.6
9°	1766.8
10°	1682.7
11°	1591.8
12°	1495.5
13°	1394.8
14°	1292.5
15°	1190.2
17.5°	938.7
20°	718.2
22.5°	532.6
25°	394.0
27.5°	286.4
30°	209.1
32.5°	150.8
35°	107.6
37.5°	75.0
40°	53.0
42.5°	37.1
45°	26.5
47.5°	18.2
50°	12.9
52.5°	9.1
55°	7.6
57.5°	6.8
60°	6.1
62.5°	5.3
65°	5.3
67.5°	4.5
70°	3.8
72.5°	3.0
75°	2.3
77.5°	2.3
80°	1.5
82.5°	1.5
85°	0.8
87.5°	0.0



TEST NUMBER: P1276093

CATALOG NUMBER: P3AS13R309835DE010 E3DL1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)