

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276107

Luminaire Tested: P3AS13R309835DE010 E3PHLD1MW

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276107
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R309835DE010 E3PHLD1MW
Description: 3in Adjustable LED luminaire with, R30 optic, 3500K CCT AND, 98CRI , E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 589.0 lumens
Efficiency: N/A
Efficacy: 40.6 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276107

CATALOG NUMBER: P3AS13R309835DE010 E3PHLD1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1276107

CATALOG NUMBER: P3AS13R309835DE010 E3PHLD1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94
2	104	98	93	88	102	96	91	87	93	89	85		90	86	83		87
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74
5	85	75	68	63	84	74	67	62	72	66	62		70	65	61		69
6	80	69	62	57	79	69	62	57	67	61	56		65	60	56		64
7	76	65	57	52	74	64	57	52	62	56	52		61	56	52		60
8	71	60	53	48	70	60	53	48	58	52	48		57	52	48		56
9	68	57	50	45	66	56	49	45	55	49	45		54	49	45		53
10	64	53	47	42	63	53	46	42	52	46	42		51	46	42		50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	145142
5°	138719
10°	119659
15°	99183
20°	81300
25°	65544
30°	52818
35°	43259
40°	35953
45°	30484
50°	26097
55°	22556
60°	20130
65°	17589
70°	15387
75°	12963
80°	9597
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 30484 cd/sqm

TEST NUMBER: P1276107

CATALOG NUMBER: P3AS13R309835DE010 E3PHLD1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.1	9.7
10°-20°	121.8	20.7
20°-30°	124.9	21.2
30°-40°	102.1	17.3
40°-50°	76.3	13.0
50°-60°	53.6	9.1
60°-70°	33.7	5.7
70°-80°	16.3	2.8
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	303.8	51.6
0°-40°	405.9	68.9
0°-60°	535.9	91.0
0°-90°	589.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	589.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	662	
5°	630	57
15°	437	122
25°	271	125
35°	162	102
45°	98	76
55°	59	54
65°	34	34
75°	15	16
85°	2	3
90°	0	

TEST NUMBER: P1276107

CATALOG NUMBER: P3AS13R309835DE010 E3PHLD1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	661.9
2.5°	655.3
5°	630.2
7.5°	588.7
10°	537.4
12.5°	487.1
15°	436.9
17.5°	391.0
20°	348.4
22.5°	308.0
25°	270.9
27.5°	238.1
30°	208.6
32.5°	184.6
35°	161.6
37.5°	143.1
40°	125.6
42.5°	111.4
45°	98.3
47.5°	86.3
50°	76.5
52.5°	67.7
55°	59.0
57.5°	52.4
60°	45.9
62.5°	39.3
65°	33.9
67.5°	28.4
70°	24.0
72.5°	19.7
75°	15.3
77.5°	10.9
80°	7.6
82.5°	4.4
85°	2.2
87.5°	1.1
90°	0.0

(END OF REPORT)