

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276897

Luminaire Tested: P3AS20R509835D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276897
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-31)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509835D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1793.0 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.75
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276897
CATALOG NUMBER: P3AS20R509835D010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1276897

CATALOG NUMBER: P3AS20R509835D010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94				94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87				87
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82				82
4	98	91	85	81	96	90	85	81	87	83	80	85	82	79	84	80	78	76				76
5	93	85	80	75	92	84	79	75	83	78	74	81	77	74	79	76	73	72				72
6	89	80	75	71	88	80	74	70	78	73	70	77	73	69	75	72	69	67				67
7	85	76	70	66	84	75	70	66	74	69	66	73	69	65	72	68	65	64				64
8	81	72	66	62	80	71	66	62	70	65	62	69	65	62	68	64	61	60				60
9	78	68	63	59	76	68	62	59	67	62	59	66	62	58	65	61	58	57				57
10	74	65	59	56	73	65	59	56	64	59	55	63	58	55	62	58	55	54				54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	570853
5°	559365
10°	523927
15°	469038
20°	394694
25°	301251
30°	195777
35°	116071
40°	67069
45°	33616
50°	12520
55°	9749
60°	9078
65°	8250
70°	8207
75°	8133
80°	8082
85°	8051

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 33616 cd/sqm



TEST NUMBER: P1276897

CATALOG NUMBER: P3AS20R509835D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	236.4	13.2
10°-20°	571.4	31.9
20°-30°	560.5	31.3
30°-40°	282.4	15.7
40°-50°	89.2	5.0
50°-60°	23.1	1.3
60°-70°	16.3	0.9
70°-80°	10.1	0.6
80°-90°	3.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1368.3	76.3
0°-40°	1650.7	92.1
0°-60°	1763.1	98.3
0°-90°	1793.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1793.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2603	
5°	2541	236
15°	2066	571
25°	1245	561
35°	434	282
45°	108	89
55°	26	23
65°	16	16
75°	10	10
85°	3	3
90°	0	



TEST NUMBER: P1276897
CATALOG NUMBER: P3AS20R509835D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2603.3
2.5°	2587.4
5°	2541.2
7.5°	2458.3
10°	2353.0
12.5°	2217.5
15°	2066.1
17.5°	1890.7
20°	1691.4
22.5°	1476.2
25°	1245.1
27.5°	999.6
30°	773.2
32.5°	581.9
35°	433.6
37.5°	320.4
40°	234.3
42.5°	165.8
45°	108.4
47.5°	62.2
50°	36.7
52.5°	27.1
55°	25.5
57.5°	22.3
60°	20.7
62.5°	19.1
65°	15.9
67.5°	14.3
70°	12.8
72.5°	11.2
75°	9.6
77.5°	8.0
80°	6.4
82.5°	4.8
85°	3.2
87.5°	1.6
90°	0.0

(END OF REPORT)