

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276898

Luminaire Tested: P3AS20R509835D010 E3DLD1GPH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276898  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS20R509835D010 E3DLD1GPH  
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 684.0 lumens  
Efficiency: N/A  
Efficacy: 25.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 27.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276898  
CATALOG NUMBER: P3AS20R509835D010 E3DLD1GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P1276898

CATALOG NUMBER: P3AS20R509835D010 E3DLD1GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83			83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75			75
4	93	85	78	73	91	83	77	73	81	76	72	79	75	71	77	73	70	69			69
5	88	78	72	67	86	77	71	66	75	70	66	74	69	65	72	68	64	63			63
6	83	73	66	61	81	72	65	61	70	65	60	69	64	60	67	63	59	58			58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	53			53
8	74	63	57	52	73	63	56	52	61	56	52	60	55	51	59	55	51	50			50
9	70	59	53	48	69	59	52	48	58	52	48	57	52	48	56	51	48	46			46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43			43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	139002
5°	136958
10°	130882
15°	121227
20°	108929
25°	95764
30°	81430
35°	66040
40°	49607
45°	31941
50°	15181
55°	11928
60°	11315
65°	10533
70°	9489
75°	8557
80°	7829
85°	7799

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 31941 cd/sqm



TEST NUMBER: P1276898  
 CATALOG NUMBER: P3AS20R509835D010 E3DLD1GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.3	8.5
10°-20°	148.9	21.8
20°-30°	180.9	26.4
30°-40°	153.4	22.4
40°-50°	79.7	11.6
50°-60°	28.7	4.2
60°-70°	19.9	2.9
70°-80°	10.8	1.6
80°-90°	3.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.1	56.7
0°-40°	541.5	79.2
0°-60°	649.9	95.0
0°-90°	684.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	684.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	634	
5°	622	58
15°	534	149
25°	396	181
35°	247	153
45°	103	80
55°	31	29
65°	20	20
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P1276898  
CATALOG NUMBER: P3AS20R509835D010 E3DLD1GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	633.9
2.5°	631.6
5°	622.2
7.5°	608.1
10°	587.8
12.5°	562.1
15°	534.0
17.5°	502.0
20°	466.8
22.5°	430.9
25°	395.8
27.5°	359.1
30°	321.6
32.5°	284.2
35°	246.7
37.5°	210.0
40°	173.3
42.5°	138.2
45°	103.0
47.5°	68.7
50°	44.5
52.5°	34.3
55°	31.2
57.5°	28.1
60°	25.8
62.5°	22.6
65°	20.3
67.5°	17.2
70°	14.8
72.5°	12.5
75°	10.1
77.5°	7.8
80°	6.2
82.5°	4.7
85°	3.1
87.5°	1.6
90°	0.0

(END OF REPORT)