

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276110

Luminaire Tested: P3AS13R359835DE010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276110
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359835DE010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 962.0 lumens
Efficiency: N/A
Efficacy: 66.3 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276110

CATALOG NUMBER: P3AS13R359835DE010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1276110

CATALOG NUMBER: P3AS13R359835DE010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	627296
5°	614504
10°	571688
15°	419117
20°	214615
25°	77351
30°	30106
35°	10547
40°	4351
45°	1178
50°	1023
55°	1147
60°	1009
65°	778
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1344 cd/sqm

TEST NUMBER: P1276110

CATALOG NUMBER: P3AS13R359835DE010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	260.3	27.1
10°-20°	488.3	50.8
20°-30°	172.9	18.0
30°-40°	30.3	3.1
40°-50°	4.4	0.5
50°-60°	2.4	0.3
60°-70°	1.8	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	921.5	95.8
0°-40°	951.7	98.9
0°-60°	958.6	99.6
0°-90°	962.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	962.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2861	
5°	2792	260
15°	1846	488
25°	320	173
35°	39	30
45°	4	4
55°	3	2
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1276110

CATALOG NUMBER: P3AS13R359835DE010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

0°	
0°	2860.7
1°	2859.9
2°	2850.8
3°	2833.4
4°	2817.5
5°	2791.7
6°	2765.2
7°	2735.7
8°	2699.3
9°	2642.5
10°	2567.5
11°	2463.7
12°	2338.7
13°	2190.2
14°	2026.6
15°	1846.2
17.5°	1375.0
20°	919.7
22.5°	554.6
25°	319.7
27.5°	190.9
30°	118.9
32.5°	68.9
35°	39.4
37.5°	25.0
40°	15.2
42.5°	7.6
45°	3.8
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	2.3
60°	2.3
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1276110
CATALOG NUMBER: P3AS13R359835DE010 E3CB1MMS

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)