

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276904

Luminaire Tested: P3AS20R509835D010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R509835D010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R50 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 577.0 lumens
Efficiency: N/A
Efficacy: 21.1 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276904

CATALOG NUMBER: P3AS20R509835D010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276904

CATALOG NUMBER: P3AS20R509835D010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	101	95	89	85	99	93	88	85	91	87	83		88	85	82		86
4	96	88	82	78	94	87	82	78	85	80	77		83	79	76		81
5	91	83	76	72	90	82	76	72	80	75	71		78	74	70		77
6	87	77	71	67	85	77	71	67	75	70	66		74	69	66		72
7	82	73	67	62	81	72	66	62	71	66	62		70	65	61		68
8	78	69	63	58	77	68	62	58	67	62	58		66	61	58		65
9	75	65	59	55	74	64	59	55	63	58	55		63	58	54		62
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	167816
5°	163306
10°	150587
15°	132441
20°	110796
25°	87852
30°	64466
35°	44330
40°	28167
45°	15754
50°	8529
55°	7149
60°	6184
65°	5656
70°	5001
75°	4660
80°	3915
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15754 cd/sqm

TEST NUMBER: P1276904

CATALOG NUMBER: P3AS20R509835D010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.7	11.9
10°-20°	161.6	28.0
20°-30°	165.3	28.6
30°-40°	104.8	18.2
40°-50°	41.7	7.2
50°-60°	16.9	2.9
60°-70°	10.8	1.9
70°-80°	5.5	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	395.6	68.6
0°-40°	500.3	86.7
0°-60°	558.9	96.9
0°-90°	577.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	577.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	765	
5°	742	69
15°	583	162
25°	363	165
35°	166	105
45°	51	42
55°	19	17
65°	11	11
75°	6	6
85°	2	2
90°	0	

TEST NUMBER: P1276904

CATALOG NUMBER: P3AS20R509835D010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	765.3
2.5°	759.8
5°	741.9
7.5°	713.8
10°	676.3
12.5°	631.8
15°	583.4
17.5°	530.3
20°	474.8
22.5°	419.4
25°	363.1
27.5°	306.9
30°	254.6
32.5°	207.7
35°	165.6
37.5°	129.6
40°	98.4
42.5°	72.6
45°	50.8
47.5°	34.4
50°	25.0
52.5°	21.1
55°	18.7
57.5°	16.4
60°	14.1
62.5°	12.5
65°	10.9
67.5°	9.4
70°	7.8
72.5°	6.2
75°	5.5
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.6
87.5°	0.8
90°	0.0

(END OF REPORT)