

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276127

Luminaire Tested: P3AS13R359835DE010 E3DLD1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276127
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R359835DE010 E3DLD1WMH
Description: 3in Adjustable LED luminaire with, R35 optic, 3500K CCT AND, 98CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 42.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276127

CATALOG NUMBER: P3AS13R359835DE010 E3DLD1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1276127

CATALOG NUMBER: P3AS13R359835DE010 E3DLD1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91		
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83		
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76		
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69		
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64		
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59		
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55		
8	75	64	58	53	74	64	57	53	63	57	53	62	56	53	61	56	52	51		
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48		
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140033
5°	137068
10°	128365
15°	115211
20°	100225
25°	85408
30°	71530
35°	56992
40°	41191
45°	26080
50°	14226
55°	9863
60°	9298
65°	8665
70°	8271
75°	7032
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26080 cd/sqm

TEST NUMBER: P1276127

CATALOG NUMBER: P3AS13R359835DE010 E3DLD1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.9	9.5
10°-20°	141.2	23.0
20°-30°	161.9	26.4
30°-40°	132.1	21.5
40°-50°	66.6	10.9
50°-60°	24.8	4.0
60°-70°	16.6	2.7
70°-80°	9.2	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	361.0	58.9
0°-40°	493.1	80.4
0°-60°	584.5	95.3
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	639	
5°	623	58
15°	508	141
25°	353	162
35°	213	132
45°	84	67
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1276127

CATALOG NUMBER: P3AS13R359835DE010 E3DLD1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	638.6
1°	637.8
2°	636.3
3°	633.3
4°	628.7
5°	622.7
6°	615.1
7°	607.5
8°	597.7
9°	587.8
10°	576.5
11°	564.3
12°	551.5
13°	537.1
14°	521.9
15°	507.5
17.5°	468.9
20°	429.5
22.5°	389.4
25°	353.0
27.5°	317.4
30°	282.5
32.5°	247.7
35°	212.9
37.5°	178.0
40°	143.9
42.5°	112.1
45°	84.1
47.5°	60.6
50°	41.7
52.5°	30.3
55°	25.8
57.5°	23.5
60°	21.2
62.5°	18.9
65°	16.7
67.5°	14.4
70°	12.9
72.5°	10.6
75°	8.3
77.5°	6.8
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1276127

CATALOG NUMBER: P3AS13R359835DE010 E3DLD1WMH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)