

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276155

Luminaire Tested: P3AS13R409835DE010 E3DLD1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276155
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409835DE010 E3DLD1H
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 677.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276155
CATALOG NUMBER: P3AS13R409835DE010 E3DLD1H

Luminous Intensity Polar Plot





TEST NUMBER: P1276155
 CATALOG NUMBER: P3AS13R409835DE010 E3DLD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	61	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151962
5°	149218
10°	140656
15°	127765
20°	112243
25°	95836
30°	79405
35°	61221
40°	43567
45°	29367
50°	16034
55°	11278
60°	10613
65°	9806
70°	8719
75°	8303
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 29367 cd/sqm



TEST NUMBER: P1276155
 CATALOG NUMBER: P3AS13R409835DE010 E3DLD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	9.3
10°-20°	156.8	23.2
20°-30°	181.2	26.8
30°-40°	142.8	21.1
40°-50°	73.3	10.8
50°-60°	28.0	4.1
60°-70°	18.5	2.7
70°-80°	10.1	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.2	59.3
0°-40°	544.0	80.4
0°-60°	645.4	95.3
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	693	
5°	678	63
15°	563	157
25°	396	181
35°	229	143
45°	95	73
55°	30	28
65°	19	19
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1276155
CATALOG NUMBER: P3AS13R409835DE010 E3DLD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	693.0
2.5°	689.3
5°	677.9
7.5°	658.2
10°	631.7
12.5°	600.6
15°	562.8
17.5°	523.4
20°	481.0
22.5°	437.8
25°	396.1
27.5°	354.5
30°	313.6
32.5°	271.9
35°	228.7
37.5°	188.6
40°	152.2
42.5°	121.2
45°	94.7
47.5°	68.9
50°	47.0
52.5°	34.1
55°	29.5
57.5°	26.5
60°	24.2
62.5°	21.2
65°	18.9
67.5°	15.9
70°	13.6
72.5°	11.4
75°	9.8
77.5°	7.6
80°	5.3
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)