

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276156

Luminaire Tested: P3AS13R409835DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276156
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R409835DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R40 optic, 3500K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 677.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276156

CATALOG NUMBER: P3AS13R409835DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1276156

CATALOG NUMBER: P3AS13R409835DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64
8	75	64	58	53	74	64	58	53	63	57	53		62	56	53		61
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	151962
5°	149218
10°	140656
15°	127765
20°	112243
25°	95836
30°	79405
35°	61221
40°	43567
45°	29367
50°	16034
55°	11278
60°	10613
65°	9806
70°	8719
75°	8303
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29367 cd/sqm

TEST NUMBER: P1276156

CATALOG NUMBER: P3AS13R409835DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	9.3
10°-20°	156.8	23.2
20°-30°	181.2	26.8
30°-40°	142.8	21.1
40°-50°	73.3	10.8
50°-60°	28.0	4.1
60°-70°	18.5	2.7
70°-80°	10.1	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	401.2	59.3
0°-40°	544.0	80.4
0°-60°	645.4	95.3
0°-90°	677.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	677.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	693	
5°	678	63
15°	563	157
25°	396	181
35°	229	143
45°	95	73
55°	30	28
65°	19	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1276156

CATALOG NUMBER: P3AS13R409835DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	693.0
2.5°	689.3
5°	677.9
7.5°	658.2
10°	631.7
12.5°	600.6
15°	562.8
17.5°	523.4
20°	481.0
22.5°	437.8
25°	396.1
27.5°	354.5
30°	313.6
32.5°	271.9
35°	228.7
37.5°	188.6
40°	152.2
42.5°	121.2
45°	94.7
47.5°	68.9
50°	47.0
52.5°	34.1
55°	29.5
57.5°	26.5
60°	24.2
62.5°	21.2
65°	18.9
67.5°	15.9
70°	13.6
72.5°	11.4
75°	9.8
77.5°	7.6
80°	5.3
82.5°	4.5
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)