

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276169

Luminaire Tested: P3AS13R459835DE010 E3CD1MB

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276169
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-28)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459835DE010 E3CD1MB
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1015.0 lumens
Efficiency: N/A
Efficacy: 70.0 lumens/watt
Spacing Criteria (0/90/45): 0.72 / 0.72 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276169

CATALOG NUMBER: P3AS13R459835DE010 E3CD1MB

Luminous Intensity Polar Plot



TEST NUMBER: P1276169

CATALOG NUMBER: P3AS13R459835DE010 E3CD1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95		
2	110	106	102	100	108	104	101	98	101	98	96	98	96	94	95	94	92	91		
3	106	100	96	93	104	99	95	92	96	93	91	94	91	89	92	90	88	86		
4	102	95	91	87	100	94	90	87	92	89	86	90	87	85	88	86	84	82		
5	98	91	86	82	96	90	85	82	88	84	81	87	83	81	85	82	80	79		
6	94	87	82	78	93	86	81	78	85	80	77	83	80	77	82	79	76	75		
7	90	83	78	74	89	82	78	74	81	77	74	80	76	74	79	76	73	72		
8	87	79	74	71	86	79	74	71	78	74	71	77	73	70	76	73	70	69		
9	84	76	71	68	83	76	71	68	75	71	68	74	70	67	73	70	67	66		
10	81	73	68	65	80	73	68	65	72	68	65	71	67	65	71	67	65	64		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	440052
5°	442416
10°	428805
15°	359344
20°	274681
25°	167211
30°	69580
35°	22299
40°	6927
45°	1395
50°	1023
55°	1147
60°	1009
65°	1193
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1395 cd/sqm

TEST NUMBER: P1276169

CATALOG NUMBER: P3AS13R459835DE010 E3CD1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.6	18.7
10°-20°	435.1	42.9
20°-30°	313.2	30.9
30°-40°	65.2	6.4
40°-50°	5.9	0.6
50°-60°	2.4	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	937.8	92.4
0°-40°	1003.0	98.8
0°-60°	1011.4	99.6
0°-90°	1015.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1015.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2007	
5°	2010	190
15°	1583	435
25°	691	313
35°	83	65
45°	4	6
55°	3	2
65°	2	2
75°	2	1
85°	0	0
90°	0	

TEST NUMBER: P1276169

CATALOG NUMBER: P3AS13R459835DE010 E3CD1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2006.8
2.5°	2007.6
5°	2009.9
7.5°	1995.5
10°	1925.8
12.5°	1780.5
15°	1582.9
17.5°	1380.8
20°	1177.1
22.5°	943.2
25°	691.1
27.5°	455.7
30°	274.8
32.5°	153.7
35°	83.3
37.5°	46.9
40°	24.2
42.5°	10.6
45°	4.5
47.5°	3.0
50°	3.0
52.5°	3.0
55°	3.0
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)