

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276177

Luminaire Tested: P3AS13R459835DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276177
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459835DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 546.0 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276177
CATALOG NUMBER: P3AS13R459835DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276177

CATALOG NUMBER: P3AS13R459835DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93			93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86			86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79			79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74			74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69			69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64			64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60			60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56			56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53			53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50			50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	162640
5°	158925
10°	146602
15°	127470
20°	104729
25°	81489
30°	60161
35°	42349
40°	26421
45°	14327
50°	7744
55°	6652
60°	5964
65°	5085
70°	4360
75°	4490
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 14327 cd/sqm



TEST NUMBER: P1276177
 CATALOG NUMBER: P3AS13R459835DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.9	12.2
10°-20°	155.2	28.4
20°-30°	154.1	28.2
30°-40°	99.3	18.2
40°-50°	38.2	7.0
50°-60°	15.5	2.8
60°-70°	9.8	1.8
70°-80°	5.3	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	376.2	68.9
0°-40°	475.5	87.1
0°-60°	529.2	96.9
0°-90°	546.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	546.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	742	
5°	722	67
15°	562	155
25°	337	154
35°	158	99
45°	46	38
55°	17	16
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1276177
CATALOG NUMBER: P3AS13R459835DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	741.7
2.5°	737.9
5°	722.0
7.5°	694.7
10°	658.4
12.5°	613.0
15°	561.5
17.5°	505.5
20°	448.8
22.5°	391.3
25°	336.8
27.5°	285.3
30°	237.6
32.5°	196.0
35°	158.2
37.5°	124.1
40°	92.3
42.5°	66.6
45°	46.2
47.5°	31.0
50°	22.7
52.5°	18.9
55°	17.4
57.5°	15.1
60°	13.6
62.5°	11.4
65°	9.8
67.5°	8.3
70°	6.8
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)