

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276178

Luminaire Tested: P3AS13R459835DE010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276178
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459835DE010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 847.0 lumens
Efficiency: N/A
Efficacy: 58.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276178

CATALOG NUMBER: P3AS13R459835DE010 E3DL1WMH

Luminous Intensity Polar Plot



TEST NUMBER: P1276178

CATALOG NUMBER: P3AS13R459835DE010 E3DL1WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98
2	109	104	100	97	106	102	99	96	99	96	94		96	94	92		93
3	104	98	93	89	102	96	92	88	94	90	87		91	88	86		89
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85
5	94	87	81	77	93	86	81	77	84	80	76		82	79	76		81
6	90	82	76	73	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74
8	83	74	68	65	82	73	68	64	72	68	64		71	67	64		70
9	79	70	65	61	78	70	65	61	69	64	61		68	64	61		67
10	76	67	62	58	75	67	62	58	66	61	58		65	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318089
5°	310631
10°	285544
15°	241954
20°	187710
25°	131209
30°	82671
35°	48666
40°	27537
45°	13397
50°	4640
55°	3747
60°	3640
65°	3528
70°	3398
75°	3219
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13397 cd/sqm

TEST NUMBER: P1276178

CATALOG NUMBER: P3AS13R459835DE010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	15.4
10°-20°	292.7	34.6
20°-30°	248.5	29.3
30°-40°	118.6	14.0
40°-50°	35.7	4.2
50°-60°	9.0	1.1
60°-70°	6.8	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	671.8	79.3
0°-40°	790.4	93.3
0°-60°	835.1	98.6
0°-90°	847.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	847.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1451	
5°	1411	131
15°	1066	293
25°	542	249
35°	182	119
45°	43	36
55°	10	9
65°	7	7
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P1276178

CATALOG NUMBER: P3AS13R459835DE010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1450.6
2.5°	1441.5
5°	1411.2
7.5°	1358.9
10°	1282.4
12.5°	1180.9
15°	1065.8
17.5°	937.7
20°	804.4
22.5°	668.8
25°	542.3
27.5°	427.2
30°	326.5
32.5°	245.4
35°	181.8
37.5°	134.1
40°	96.2
42.5°	66.7
45°	43.2
47.5°	24.2
50°	13.6
52.5°	10.6
55°	9.8
57.5°	9.1
60°	8.3
62.5°	7.6
65°	6.8
67.5°	6.1
70°	5.3
72.5°	4.5
75°	3.8
77.5°	3.0
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)