

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276185

Luminaire Tested: P3AS13R459835DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276185
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R459835DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R45 optic, 3500K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 268.0 lumens
Efficiency: N/A
Efficacy: 18.5 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276185

CATALOG NUMBER: P3AS13R459835DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1276185

CATALOG NUMBER: P3AS13R459835DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91
3	102	95	90	85	100	93	89	85	91	87	83		88	85	82		86
4	96	88	83	78	94	87	82	78	85	81	77		83	79	76		81
5	91	83	77	72	90	82	76	72	80	75	71		78	74	71		77
6	87	78	72	67	85	77	71	67	75	70	66		74	69	66		73
7	83	73	67	63	81	72	67	63	71	66	62		70	65	62		69
8	79	69	63	59	77	68	63	59	67	62	58		66	62	58		65
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62
10	72	62	56	52	71	61	56	52	61	55	52		60	55	52		59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	79818
5°	78010
10°	71965
15°	62566
20°	51408
25°	39994
30°	29524
35°	20773
40°	12967
45°	7039
50°	3787
55°	3250
60°	2938
65°	2491
70°	2116
75°	2203
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7039 cd/sqm

TEST NUMBER: P1276185

CATALOG NUMBER: P3AS13R459835DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	32.8	12.2
10°-20°	76.2	28.4
20°-30°	75.6	28.2
30°-40°	48.7	18.2
40°-50°	18.8	7.0
50°-60°	7.6	2.8
60°-70°	4.8	1.8
70°-80°	2.6	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	184.6	68.9
0°-40°	233.4	87.1
0°-60°	259.7	96.9
0°-90°	268.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	268.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	364	
5°	354	33
15°	276	76
25°	165	76
35°	78	49
45°	23	19
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1276185

CATALOG NUMBER: P3AS13R459835DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	364.0
2.5°	362.2
5°	354.4
7.5°	341.0
10°	323.2
12.5°	300.9
15°	275.6
17.5°	248.1
20°	220.3
22.5°	192.0
25°	165.3
27.5°	140.0
30°	116.6
32.5°	96.2
35°	77.6
37.5°	60.9
40°	45.3
42.5°	32.7
45°	22.7
47.5°	15.2
50°	11.1
52.5°	9.3
55°	8.5
57.5°	7.4
60°	6.7
62.5°	5.6
65°	4.8
67.5°	4.1
70°	3.3
72.5°	3.0
75°	2.6
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)