

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276998

Luminaire Tested: P3AS20R709835D010 E3CB1MMS

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276998
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-48)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R709835D010 E3CB1MMS
Description: 3in Adjustable LED luminaire with, R70 optic, 3500K CCT AND, 98CRI , E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1994.1 lumens
Efficiency: N/A
Efficacy: 72.8 lumens/watt
Spacing Criteria (0/90/45): 1.01 / 1.01 / 1.03
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276998

CATALOG NUMBER: P3AS20R709835D010 E3CB1MMS

Luminous Intensity Polar Plot



TEST NUMBER: P1276998

CATALOG NUMBER: P3AS20R709835D010 E3CB1MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	111	108	106	103	104	102	100		100	99	97		97
2	107	102	97	94	105	100	96	93	97	94	91		94	91	89		91
3	101	94	89	85	99	93	88	84	90	86	83		88	84	81		85
4	95	87	81	77	94	86	81	76	84	79	75		82	78	75		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	75	69	64	83	75	69	64	73	68	64		72	67	63		70
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66
8	76	66	59	55	75	65	59	55	64	58	55		63	58	54		62
9	72	62	55	51	71	61	55	51	60	55	51		59	54	50		58
10	68	58	52	47	67	57	51	47	56	51	47		56	51	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	395955
5°	377811
10°	359468
15°	349854
20°	336939
25°	318889
30°	296603
35°	249141
40°	160587
45°	74643
50°	19581
55°	4855
60°	4912
65°	4151
70°	4103
75°	4067
80°	4041
85°	4026

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 74643 cd/sqm

TEST NUMBER: P1276998

CATALOG NUMBER: P3AS20R709835D010 E3CB1MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	8.1
10°-20°	433.0	21.7
20°-30°	605.0	30.3
30°-40°	561.0	28.1
40°-50°	201.1	10.1
50°-60°	17.0	0.9
60°-70°	8.5	0.4
70°-80°	5.5	0.3
80°-90°	2.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1198.7	60.1
0°-40°	1759.7	88.2
0°-60°	1977.9	99.2
0°-90°	1994.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1994.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1806	
5°	1716	161
15°	1541	433
25°	1318	605
35°	931	561
45°	241	201
55°	13	17
65°	8	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1276998

CATALOG NUMBER: P3AS20R709835D010 E3CB1MMS

CANDELA DISTRIBUTION (FULL):

	0°
0°	1805.7
2.5°	1778.6
5°	1716.4
7.5°	1659.1
10°	1614.4
12.5°	1577.8
15°	1541.1
17.5°	1496.5
20°	1443.9
22.5°	1383.4
25°	1318.0
27.5°	1251.1
30°	1171.4
32.5°	1069.4
35°	930.7
37.5°	753.8
40°	561.0
42.5°	382.5
45°	240.7
47.5°	133.9
50°	57.4
52.5°	19.1
55°	12.7
57.5°	11.2
60°	11.2
62.5°	9.6
65°	8.0
67.5°	8.0
70°	6.4
72.5°	6.4
75°	4.8
77.5°	4.8
80°	3.2
82.5°	3.2
85°	1.6
87.5°	1.6
90°	0.0

(END OF REPORT)