

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276258

Luminaire Tested: P3AS13R609835DE010 E3D1WH

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276258
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-15)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609835DE010 E3D1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3D1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 907.0 lumens
Efficiency: N/A
Efficacy: 62.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276258
CATALOG NUMBER: P3AS13R609835DE010 E3D1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276258
 CATALOG NUMBER: P3AS13R609835DE010 E3D1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | | | 0 | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1 | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 94 | 94 | 94 | 94 |
| 2 | 108 | 104 | 100 | 96 | 106 | 102 | 98 | 95 | 99 | 96 | 93 | 96 | 93 | 91 | 93 | 91 | 89 | 88 | 88 | 88 | 88 |
| 3 | 103 | 97 | 92 | 88 | 101 | 96 | 91 | 88 | 93 | 89 | 86 | 91 | 87 | 85 | 88 | 86 | 84 | 82 | 82 | 82 | 82 |
| 4 | 98 | 91 | 85 | 81 | 96 | 90 | 85 | 81 | 88 | 83 | 80 | 86 | 82 | 79 | 84 | 81 | 78 | 77 | 77 | 77 | 77 |
| 5 | 93 | 85 | 80 | 75 | 92 | 84 | 79 | 75 | 83 | 78 | 74 | 81 | 77 | 74 | 79 | 76 | 73 | 72 | 72 | 72 | 72 |
| 6 | 89 | 80 | 74 | 70 | 87 | 79 | 74 | 70 | 78 | 73 | 70 | 77 | 72 | 69 | 75 | 71 | 69 | 67 | 67 | 67 | 67 |
| 7 | 85 | 76 | 70 | 66 | 83 | 75 | 69 | 65 | 74 | 69 | 65 | 72 | 68 | 65 | 71 | 67 | 64 | 63 | 63 | 63 | 63 |
| 8 | 81 | 71 | 65 | 61 | 79 | 71 | 65 | 61 | 70 | 65 | 61 | 69 | 64 | 61 | 68 | 64 | 61 | 59 | 59 | 59 | 59 |
| 9 | 77 | 67 | 62 | 58 | 76 | 67 | 61 | 58 | 66 | 61 | 57 | 65 | 61 | 57 | 64 | 60 | 57 | 56 | 56 | 56 | 56 |
| 10 | 73 | 64 | 58 | 54 | 72 | 63 | 58 | 54 | 63 | 58 | 54 | 62 | 57 | 54 | 61 | 57 | 54 | 53 | 53 | 53 | 53 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 237656 |
| 5° | 224345 |
| 10° | 218522 |
| 15° | 213509 |
| 20° | 198537 |
| 25° | 177470 |
| 30° | 135565 |
| 35° | 78273 |
| 40° | 30371 |
| 45° | 12652 |
| 50° | 2797 |
| 55° | 421 |
| 60° | 307 |
| 65° | 208 |
| 70° | 256 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12652 cd/sqm



TEST NUMBER: P1276258
 CATALOG NUMBER: P3AS13R609835DE010 E3D1WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 96.2 | 10.6 |
| 10°-20° | 262.0 | 28.9 |
| 20°-30° | 328.1 | 36.2 |
| 30°-40° | 183.4 | 20.2 |
| 40°-50° | 34.9 | 3.8 |
| 50°-60° | 1.8 | 0.2 |
| 60°-70° | 0.4 | 0.0 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 686.4 | 75.7 |
| 0°-40° | 869.8 | 95.9 |
| 0°-60° | 906.4 | 99.9 |
| 0°-90° | 907.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 907.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1084 | |
| 5° | 1019 | 96 |
| 15° | 940 | 262 |
| 25° | 734 | 328 |
| 35° | 292 | 183 |
| 45° | 41 | 35 |
| 55° | 1 | 2 |
| 65° | 0 | 0 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P1276258
CATALOG NUMBER: P3AS13R609835DE010 E3D1WH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1083.8 |
| 1° | 1079.3 |
| 2° | 1065.2 |
| 3° | 1048.5 |
| 4° | 1032.9 |
| 5° | 1019.2 |
| 6° | 1008.8 |
| 7° | 999.9 |
| 8° | 993.2 |
| 9° | 986.9 |
| 10° | 981.4 |
| 11° | 975.8 |
| 12° | 969.5 |
| 13° | 961.7 |
| 14° | 952.4 |
| 15° | 940.5 |
| 16° | 926.1 |
| 17° | 909.7 |
| 18° | 891.2 |
| 19° | 870.0 |
| 20° | 850.8 |
| 21° | 830.0 |
| 22° | 808.5 |
| 23° | 785.8 |
| 24° | 761.0 |
| 25° | 733.5 |
| 26° | 701.2 |
| 27° | 665.2 |
| 28° | 624.8 |
| 29° | 581.8 |
| 30° | 535.4 |
| 31° | 488.6 |
| 32° | 440.4 |
| 32.5° | 414.1 |
| 33° | 390.3 |
| 34° | 341.0 |
| 35° | 292.4 |
| 36° | 248.6 |
| 37° | 202.2 |
| 37.5° | 181.1 |
| 38° | 160.3 |
| 39° | 129.1 |
| 40° | 106.1 |
| 42.5° | 64.6 |
| 45° | 40.8 |



TEST NUMBER: P1276258
CATALOG NUMBER: P3AS13R609835DE010 E3D1WH

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 47.5° | 22.6 |
| 50° | 8.2 |
| 52.5° | 1.9 |
| 55° | 1.1 |
| 57.5° | 0.7 |
| 60° | 0.7 |
| 62.5° | 0.4 |
| 65° | 0.4 |
| 67.5° | 0.4 |
| 70° | 0.4 |
| 72.5° | 0.4 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)