

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276264

Luminaire Tested: P3AS13R609835DE010 E3DL1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R609835DE010 E3DL1WH
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 551.0 lumens
Efficiency: N/A
Efficacy: 38.0 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276264
CATALOG NUMBER: P3AS13R609835DE010 E3DL1WH

Luminous Intensity Polar Plot





TEST NUMBER: P1276264
 CATALOG NUMBER: P3AS13R609835DE010 E3DL1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85				85
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	139638
5°	136517
10°	127809
15°	114666
20°	98592
25°	81537
30°	64415
35°	47837
40°	32947
45°	20653
50°	11360
55°	6652
60°	5964
65°	5085
70°	4360
75°	4490
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 20653 cd/sqm



TEST NUMBER: P1276264
 CATALOG NUMBER: P3AS13R609835DE010 E3DL1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	10.5
10°-20°	140.3	25.5
20°-30°	153.9	27.9
30°-40°	112.1	20.3
40°-50°	52.9	9.6
50°-60°	17.3	3.1
60°-70°	9.8	1.8
70°-80°	5.3	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.9	63.9
0°-40°	464.0	84.2
0°-60°	534.2	97.0
0°-90°	551.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	551.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	637	
5°	620	58
15°	505	140
25°	337	154
35°	179	112
45°	67	53
55°	17	17
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1276264

CATALOG NUMBER: P3AS13R609835DE010 E3DL1WH

CANDELA DISTRIBUTION (FULL):

	0°
0°	636.8
2.5°	633.0
5°	620.2
7.5°	600.5
10°	574.0
12.5°	542.2
15°	505.1
17.5°	464.9
20°	422.5
22.5°	379.4
25°	337.0
27.5°	294.6
30°	254.4
32.5°	215.8
35°	178.7
37.5°	145.4
40°	115.1
42.5°	88.6
45°	66.6
47.5°	48.5
50°	33.3
52.5°	22.0
55°	17.4
57.5°	15.1
60°	13.6
62.5°	11.4
65°	9.8
67.5°	8.3
70°	6.8
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)