

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276265

Luminaire Tested: P3AS13R609835DE010 E3DL1WMH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1276265  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRIS  
Catalog Number: P3AS13R609835DE010 E3DL1WMH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3500K CCT AND, 98CRI , E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 797.0 lumens  
Efficiency: N/A  
Efficacy: 55.0 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1276265  
CATALOG NUMBER: P3AS13R609835DE010 E3DL1WMH

### Luminous Intensity Polar Plot



TEST NUMBER: P1276265  
 CATALOG NUMBER: P3AS13R609835DE010 E3DL1WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	108	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93	93	93	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85	85	85	85
3	101	95	89	85	99	93	88	84	91	86	83	88	85	82	86	83	80	79	79	79	79
4	96	88	82	78	94	87	81	77	85	80	76	83	79	75	81	77	75	73	73	73	73
5	91	82	76	71	89	81	75	71	79	74	70	78	73	70	76	72	69	68	68	68	68
6	86	77	70	66	84	76	70	66	74	69	65	73	68	65	72	68	64	63	63	63	63
7	82	72	66	61	80	71	65	61	70	65	61	69	64	60	68	63	60	59	59	59	59
8	77	68	61	57	76	67	61	57	66	60	57	65	60	56	64	59	56	55	55	55	55
9	74	64	57	53	72	63	57	53	62	57	53	61	56	53	60	56	53	51	51	51	51
10	70	60	54	50	69	60	54	50	59	53	50	58	53	50	57	53	49	48	48	48	48

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	188187
5°	186418
10°	180981
15°	169558
20°	150070
25°	125548
30°	98395
35°	71367
40°	47489
45°	29584
50°	16034
55°	4626
60°	4298
65°	3943
70°	3911
75°	3813
80°	3788
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 29584 cd/sqm



TEST NUMBER: P1276265  
 CATALOG NUMBER: P3AS13R609835DE010 E3DL1WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	79.7	10.0
10°-20°	207.2	26.0
20°-30°	236.2	29.6
30°-40°	167.5	21.0
40°-50°	76.0	9.5
50°-60°	16.1	2.0
60°-70°	7.8	1.0
70°-80°	4.8	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	523.2	65.6
0°-40°	690.6	86.7
0°-60°	782.8	98.2
0°-90°	797.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	797.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	858	
5°	847	80
15°	747	207
25°	519	236
35°	267	167
45°	95	76
55°	12	16
65°	8	8
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1276265  
CATALOG NUMBER: P3AS13R609835DE010 E3DL1WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	858.2
2.5°	855.2
5°	846.9
7.5°	832.5
10°	812.8
12.5°	784.8
15°	746.9
17.5°	699.2
20°	643.1
22.5°	582.5
25°	518.9
27.5°	453.7
30°	388.6
32.5°	326.5
35°	266.6
37.5°	213.6
40°	165.9
42.5°	125.7
45°	95.4
47.5°	71.2
50°	47.0
52.5°	22.0
55°	12.1
57.5°	10.6
60°	9.8
62.5°	9.1
65°	7.6
67.5°	6.8
70°	6.1
72.5°	5.3
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)