

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1276303

Luminaire Tested: P3AS13R659835DE010 E3DLP1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1276303
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R659835DE010 E3DLP1LI
Description: 3in Adjustable LED luminaire with, R65 optic, 3500K CCT AND, 98CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 525.0 lumens
Efficiency: N/A
Efficacy: 36.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1276303
CATALOG NUMBER: P3AS13R659835DE010 E3DLP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P1276303
 CATALOG NUMBER: P3AS13R659835DE010 E3DLP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92				92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	90	88	86	85				85
3	101	94	88	84	99	92	87	83	90	85	82	87	84	81	85	82	79	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66				66
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62				62
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57				57
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54				54
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50				50
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47				47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133454
5°	130134
10°	121173
15°	108604
20°	93785
25°	78005
30°	61528
35°	45588
40°	31430
45°	19475
50°	10575
55°	6652
60°	5657
65°	5085
70°	4360
75°	3813
80°	3788
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 19475 cd/sqm



TEST NUMBER: P1276303
 CATALOG NUMBER: P3AS13R659835DE010 E3DLP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.9	10.5
10°-20°	132.9	25.3
20°-30°	147.0	28.0
30°-40°	106.8	20.3
40°-50°	50.0	9.5
50°-60°	16.8	3.2
60°-70°	9.7	1.9
70°-80°	5.1	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.9	63.8
0°-40°	441.7	84.1
0°-60°	508.5	96.9
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	609	
5°	591	55
15°	478	133
25°	322	147
35°	170	107
45°	63	50
55°	17	17
65°	10	10
75°	4	5
85°	2	2
90°	0	



TEST NUMBER: P1276303
CATALOG NUMBER: P3AS13R659835DE010 E3DLP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	608.6
2.5°	604.8
5°	591.2
7.5°	570.7
10°	544.2
12.5°	513.2
15°	478.4
17.5°	440.5
20°	401.9
22.5°	361.8
25°	322.4
27.5°	282.3
30°	243.0
32.5°	205.1
35°	170.3
37.5°	138.5
40°	109.8
42.5°	84.0
45°	62.8
47.5°	45.4
50°	31.0
52.5°	21.2
55°	17.4
57.5°	15.1
60°	12.9
62.5°	11.4
65°	9.8
67.5°	8.3
70°	6.8
72.5°	6.1
75°	4.5
77.5°	3.8
80°	3.0
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)